

WBT Performance kabelränna förformad T-shirt



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

DESIGN

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Stål
Yta: Förgalvaniserad;Polyuretan



SPECIFIKATIONER

Table 1/2

Katalognummer	Färg	Höjd (H)	Bredd (W)	Längd (L)	Hålstorlek (HS)	Radie (R)	Enhetsvikt
WBTT2X12		50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X12BA	Svart	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X18		50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg
WBTT2X18BA	Svart	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg
WBTT2X24		50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm	7.257 kg
WBTT2X24BA	Svart	50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm	7.257 kg
WBTT2X4		50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg

Katalognummer	Färg	Höjd (H)	Bredd (W)	Längd (L)	Hålstorlek (HS)	Radie (R)	Enhetsvikt
WBTT2X4BA	Svart	50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X6		50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X6BA	Svart	50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X8		50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT2X8BA	Svart	50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT6X6		152.39999999999998 mm					
WBTT2X4S4		50.8 mm					
WBTT4X12		101.6 mm					
WBTT4X12BA	Svart	101.6 mm					
WBTT4X18		101.6 mm					
WBTT4X18BA	Svart	101.6 mm					
WBTT4X24		101.6 mm					
WBTT4X24BA	Svart	101.6 mm					

Table 2/2

Katalognummer	Färg	Höjd (H)	Bredd (W)	Längd (L)	Hålstorlek (HS)	Radie (R)	Enhetsvikt
WBTT4X4		101.6 mm					
WBTT4X4BA	Svart	101.6 mm					
WBTT4X6		101.6 mm					
WBTT4X6BA	Svart	101.6 mm					
WBTT6X12		152.4 mm					
WBTT6X12BA	Svart	152.4 mm					
WBTT6X18		152.4 mm					
WBTT6X18BA	Svart	152.4 mm					
WBTT6X24		152.4 mm					
WBTT6X24BA	Svart	152.4 mm					
WBTT6X36		152.4 mm					

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

