


# Inner Doors, ADIS



Displays and indicators can be mounted, on a surface within the enclosure while covering other components, and preventing unauthorized access.

## 功能

将安装在壁挂式机柜内的平板型门

额外安装表面提供两层通道

Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening (Machining is required). Double-bit 3 mm lock, 800 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm, adjustable depth position with AMG accessory. Workable area: H-55, W-108. 19" version available on request.

Material: Door 1.5 mm AISI 304 stainless steel and vertical top and bottom profiles 2 mm, AISI 304 stainless steel.

Protection: IP 2XC.

Finish: 400 pre-grained stainless steel.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

完成: 拉丝

材料: 不锈钢 304

## 技术参数

| 物料号       | 高度    | 宽度    | 深度   | 门尺寸         | 门锁数量 | 产品系列  |
|-----------|-------|-------|------|-------------|------|-------|
| ADIS06060 | 545mm | 492mm | 15mm | 545 x 492mm | 1    | 壁挂式安装 |
| ADIS04030 | 400mm | 300mm | 15mm | 345 x 192mm | 1    | 壁挂式安装 |
| ADIS06040 | 545mm | 292mm | 15mm | 545 x 292mm | 1    | 壁挂式安装 |
| ADIS10080 | 945mm | 692mm | 15mm | 945 x 692mm | 2    | 壁挂式安装 |

| 物料号       | 高度     | 宽度    | 深度   | 门尺寸          | 门锁数量 | 产品系列  |
|-----------|--------|-------|------|--------------|------|-------|
| ADIS05040 | 445mm  | 292mm | 15mm | 445 x 292mm  | 1    | 壁挂式安装 |
| ADIS08060 | 745mm  | 492mm | 15mm | 745 x 492mm  | 2    | 壁挂式安装 |
| ADIS12080 | 1145mm | 692mm | 15mm | 1145 x 692mm | 2    | 壁挂式安装 |
| ADIS05050 | 445mm  | 392mm | 15mm | 445 x 392mm  | 1    | 壁挂式安装 |

其他产品详情

产品

To order 19"version, please add I19 to the catalogue no, e.g. ADIS04030I19. Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE