

Rain Hoods, MSST

A stainless steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

功能

Description: To be fitted as extra protection on stainless steel enclosures. The roof is slightly sloped and has a dripstrip.

Material: 1.5 mm stainless steel AISI 304 / AISI 316L.

Finish: 400 pre-grained stainless steel.



完成: 拉丝
厚度: 1.5mm

技术参数

Table 1/2

物料号	高度	宽度	深度	材料	产品系列	外壳材料
MSST0640N	400mm	600mm	72mm	不锈钢 304	独立	低碳钢
MSST0640N-316	400mm	600mm	72mm	不锈钢 316	独立	低碳钢
MSST0650N	500mm	600mm	72mm	不锈钢 304	独立	低碳钢
MSST0650N-316	500mm	600mm	72mm	不锈钢 316	独立	低碳钢
MSST0660N	600mm	600mm	72mm	不锈钢 304	独立	低碳钢
MSST0660N-316	600mm	600mm	72mm	不锈钢 316	独立	低碳钢
MSST0840N	400mm	800mm	72mm	不锈钢 304	独立	低碳钢
MSST0840N-316	400mm	800mm	72mm	不锈钢 316	独立	低碳钢
MSST0850N	500mm	800mm	72mm	不锈钢 304	独立	低碳钢
MSST0850N-316	500mm	800mm	72mm	不锈钢 316	独立	低碳钢

物料号	高度	宽度	深度	材料	产品系列	外壳材料
MSST0860N	600mm	800mm	72mm	不锈钢 304	独立	低碳钢
MSST0860N-316	600mm	800mm	72mm	不锈钢 316	独立	低碳钢
MSST1040N	400mm	1000mm	72mm	不锈钢 304	独立	低碳钢
MSST1040N-316	400mm	1000mm	72mm	不锈钢 316	独立	低碳钢
MSST1050N	500mm	1000mm	72mm	不锈钢 304	独立	低碳钢
MSST1050N-316	500mm	1000mm	72mm	不锈钢 316	独立	低碳钢
MSST1060N	600mm	1000mm	72mm	不锈钢 304	独立	低碳钢
MSST1060N-316	600mm	1000mm	72mm	不锈钢 316	独立	低碳钢
MSST1240N	400mm	1200mm	72mm	不锈钢 304	独立	低碳钢
MSST1240N-316	400mm	1200mm	72mm	不锈钢 316	独立	低碳钢

Table 2/2						
物料号	高度	宽度	深度	材料	产品系列	外壳材料
MSST1250N	500mm	1200mm	72mm	不锈钢 304	独立	低碳钢
MSST1250N-316	500mm	1200mm	72mm	不锈钢 316	独立	低碳钢
MSST1260N	600mm	1200mm	72mm	不锈钢 304	独立	低碳钢
MSST1260N-316	600mm	1200mm	72mm	不锈钢 316	独立	低碳钢
MSST1640N	400mm	1600mm	72mm	不锈钢 304	独立	低碳钢
MSST1640N-316	400mm	1600mm	72mm	不锈钢 316	独立	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

