

Rain Hoods, MSST

A stainless steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

功能

Description: To be fitted as extra protection on stainless steel enclosures. The roof is slightly sloped and has a dripstrip.

Material: 1.5 mm stainless steel AISI 304 / AISI 316L.

Finish: 400 pre-grained stainless steel.



厚度: 1.5mm

完成: 拉丝

技术参数

Table 1/2

物料号	高度	宽度	深度	材料	产品系列	外壳材料
MSST0650N-316	500mm	600mm	72mm	不锈钢 316	独立	低碳钢
MSST0640N-316	400mm	600mm	72mm	不锈钢 316	独立	低碳钢
MSST0860N	600mm	800mm	72mm	不锈钢 304	独立	低碳钢
MSST1060N	600mm	1000mm	72mm	不锈钢 304	独立	低碳钢
MSST0850N-316	500mm	800mm	72mm	不锈钢 316	独立	低碳钢
MSST1260N-316	600mm	1200mm	72mm	不锈钢 316	独立	低碳钢
MSST0650N	500mm	600mm	72mm	不锈钢 304	独立	低碳钢
MSST1060N-316	600mm	1000mm	72mm	不锈钢 316	独立	低碳钢
MSST0850N	500mm	800mm	72mm	不锈钢 304	独立	低碳钢
MSST1260N	600mm	1200mm	72mm	不锈钢 304	独立	低碳钢

物料号	高度	宽度	深度	材料	产品系列	外壳材料
MSST1040N-316	400mm	1000mm	72mm	不锈钢 316	独立	低碳钢
MSST1240N	400mm	1200mm	72mm	不锈钢 304	独立	低碳钢
MSST0840N-316	400mm	800mm	72mm	不锈钢 316	独立	低碳钢
MSST0840N	400mm	800mm	72mm	不锈钢 304	独立	低碳钢
MSST1250N-316	500mm	1200mm	72mm	不锈钢 316	独立	低碳钢
MSST0660N	600mm	600mm	72mm	不锈钢 304	独立	低碳钢
MSST1240N-316	400mm	1200mm	72mm	不锈钢 316	独立	低碳钢
MSST0660N-316	600mm	600mm	72mm	不锈钢 316	独立	低碳钢
MSST1250N	500mm	1200mm	72mm	不锈钢 304	独立	低碳钢
MSST1050N	500mm	1000mm	72mm	不锈钢 304	独立	低碳钢

Table 2/2						
物料号	高度	宽度	深度	材料	产品系列	外壳材料
MSST1640N	400mm	1600mm	72mm	不锈钢 304	独立	低碳钢
MSST0640N	400mm	600mm	72mm	不锈钢 304	独立	低碳钢
MSST1050N-316	500mm	1000mm	72mm	不锈钢 316	独立	低碳钢
MSST1040N	400mm	1000mm	72mm	不锈钢 304	独立	低碳钢
MSST0860N-316	600mm	800mm	72mm	不锈钢 316	独立	低碳钢
MSST1640N-316	400mm	1600mm	72mm	不锈钢 316	独立	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：

CADDY
ERICO
HOFFMAN
ILSCO
SCHROFF
TRACHTE