

EER-Ti/T Trapezoidal Deck Threaded Rod Hanger



VLASTNOSTI

Supports threaded rod

Thread impression for simple installation

Materiál: Spring Steel
Povrchová úprava: nVent CADDY Armour



SPECIFIKACE

Table 1/2

Katalogové číslo	Article Number	Hole Size (HS)	Hole Type	Flange Thickness (FT)	Drill Bit Diameter	Static Load 1 (F1)
EERTIM10	173140	10 mm	Threaded	0.8 - 3 mm	7mm	450N
EERTIM6	173120	6 mm	Threaded	0.8 - 3 mm	7mm	450N
EERTIM8	173130	8 mm	Threaded	0.8 - 3 mm	7mm	450N


Table 2/2

Katalogové číslo	Article Number	Static Load 2 (F2)	Certifications
EERTIM10	173140	900N	ITB
EERTIM6	173120	900N	
EERTIM8	173130	900N	ITB

DALŠÍ PODROBNOSTI O PRODUKTU

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/CADDY

