

nVent CADDY Speed Link SLK with Decking Hook



VLASTNOSTI

Complete system includes wire, locking device and pre-assembled decking hook end fitting

Quickly and easily attaches to hollow metal decking

Spring-loaded ends snap into decking hole and lock into place

Innovative design helps protect the wire from sharp edges of decking hole, minimizing risk of damage to wire

Materiál: Ocel; Zinc Alloy; Polypropylene
Povrchová úprava: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS



SPECIFIKACE

Katalogové číslo	Article Number	Wire Rope Diameter	Wire Rope Length	Roof Decking Sheet Thickness	A	Hole Size (HS)	Static Load
SLK15L1DH	196676	1.5 mm	1m	1.5 mm Max	9.2 mm	8 mm	195N
SLK15L2DH	196677	1.5 mm	2m	1.5 mm Max	9.2 mm	8 mm	195N
SLK15L3DH	196504	1.5 mm	3m	1.5 mm Max	9.2 mm	8 mm	195N
SLK15L5DH	196505	1.5 mm	5m	1.5 mm Max	9.2 mm	8 mm	195N
SLK2L3DH	196532	2 mm	3m	1.5 mm Max	9.2 mm	8 mm	440N
SLK2L5DH	196533	2 mm	5m	1.5 mm Max	9.2 mm	8 mm	440N


Height (H):	55 mm
Width (W):	19 mm
Thickness (T):	12.5 mm
Angle (a):	90 ° Max

DALŠÍ PODROBNOSTI O PRODUKTU

Load rating is only applicable if the load-bearing capacity of the supporting element (steel decking) is adequate.

Check with deck manufacturer for recommended load capacity.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

