

nVent CADDY Speed Link Catenary Kit



VLASTNOSTI

Kit includes pre-cut length of fuse-cut cable to avoid fraying, pre-assembled hook end fitting and tool-free locking device to save installation time

Fastens to the building structure by looping around and hooking to wire rope

Hook end-fitting easily attaches to eye nut

Spring latch helps provide secure connection

Materiál: Ocel; Zinc Alloy; Polypropylene
Povrchová úprava: Electrogalvanized; Hot-Dip Galvanized
Wire Rope Diameter: 6 mm

SPECIFIKACE

Table 1/2

Katalogové číslo	Article Number	Wire Rope Length	A	B	C	Height (H)
SLK6L10	196801	10m	75 mm	40 mm	15 mm	108 mm
SLK6L15	196802	15m	75 mm	40 mm	15 mm	108 mm
SLK6L20	196803	20m	75 mm	40 mm	15 mm	108 mm
SLK6L25	196804	25m	75 mm	40 mm	15 mm	108 mm
SLK6L30	196805	30m	75 mm	40 mm	15 mm	108 mm
SLK6L40	196806	40m	75 mm	40 mm	15 mm	108 mm
SLK6L5	196800	5m	75 mm	40 mm	15 mm	108 mm
SLK6L50	196807	50m	75 mm	40 mm	15 mm	108 mm

Table 2/2

Katalogové číslo	Article Number	Width (W)	Thickness (T)	Angle (a)
SLK6L10	196801	41 mm	30 mm	60 ° Max

Katalogové číslo	Article Number	Width (W)	Thickness (T)	Angle (a)
SLK6L15	196802	41 mm	30 mm	60 ° Max
SLK6L20	196803	41 mm	30 mm	60 ° Max
SLK6L25	196804	41 mm	30 mm	60 ° Max
SLK6L30	196805	41 mm	30 mm	60 ° Max
SLK6L40	196806	41 mm	30 mm	60 ° Max
SLK6L5	196800	41 mm	30 mm	60 ° Max
SLK6L50	196807	41 mm	30 mm	60 ° Max

DALŠÍ PODROBNOSTI O PRODUKTU


Wire Rope Length is measured from the end of the wire rope to the hook side of the swage.


Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

Horizontal Intallation		
Preload	1000 N	450 N
Static Load 1 (F1)	490 N	590 N
Static Load 2 (F2)	880 N	1080 N
Static Load 3 (F3)	980 N	1180 N
Vertical Installation		
Static Load 4 (F4)	4440 N	

DIAGRAMS





UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

