


Slim Fit vnitřní chladicí jednotka



SpectraCool SlimFit Air Conditioners are designed with three space-saving mounting options to maximize footprint. They have been developed to meet the requirements of worldwide industrial customers, easy to specify and easy to use. From filterless operation to global certifications, the SpectraCool Slim Fit Air Conditioner makes automation cooling easy for system designers and operations maintenance teams around the world.

Select units come with a Commboard for Remote Access Control (RAC), an integrated, parametric controller designed to work seamlessly with our enclosure air conditioner units for the purpose of remotely monitoring and managing anywhere from a single unit to an entire network of Spectra cool air conditioners from virtually anywhere in the world with a secure internet connection. Ensure that your systems are always running at optimal temperature levels, increase productivity and improve overall system reliability.

PRŮMYSLOVÉ NORMY

UL/cUL Listed Type 12; File No.SA6453

CE, EAC, RoHS

Cooling performance tested by TÜV SÜD Germany, according to DIN EN 14511

IP 54 internal loop, IP 34 external loop

VLASTNOSTI

Každá jednotka je před odesláním podrobena testu funkčnosti

Slim Fit Design with three mounting options; fully recessed, partial recessed and surface mount

Aesthetic design plastic cover to optimize air flow

R134a refrigerant

Voltage: 230 V (50/60 Hz), 115 V (50/60 Hz) and 400/460 V 3-phase (50/60 Hz)

Operating temperature range from 50 F / 10 C to 131 F / 55 C

Easy filter replacement for extremely dusty environments

Dust resistant coils for filterless operation

Active condensate management to prevent dripping water

Energy efficient rotary compressor

Terminal block power input

Standard cutout dimension for easy exchange

Standard Air Conditioners are compatible with an enclosure door switch

Remote Access Control Units support up to 2 temperature sensors and 10 alarms. They support multiple communication protocols: SNMP, Modbus TCP, Ethernet/IP, and Profinet.

Mounting hardware, gaskets and user manual furnished with the unit

Barva: Light Gray
Povrchová úprava: Strukturovaný Práškový
Kód barvy: RAL 7035

SPECIFIKACE

Katalogové číslo	Nominální kapacita Watt	Nominální kapacita Btu/h	Nominální napětí	Počet fází	Chladivo	Materiál
S162526G031	2500W	8500Btu/h	230V	1	R134a	Ocelový Plech
S060316G031	300W	1000Btu/h	115V	1	R134a	Ocelový Plech
S101526G031	1500W	5000Btu/h	230V	1	R134a	Ocelový Plech
S101016G031	1000W	3400Btu/h	115V	1	R134a	Ocelový Plech
S060516G031	500W	1700Btu/h	115V	1	R134a	Ocelový Plech
S101026G031	1000W	3400Btu/h	230V	1	R134a	Ocelový Plech
S060526G031	500W	1700Btu/h	230V	1	R134a	Ocelový Plech
S060326G031	300W	1000Btu/h	230V	1	R134a	Ocelový Plech
S162026G031	2000W	6800Btu/h	230V	1	R134a	Ocelový Plech
S101516G031	1500W	5000Btu/h	115V	1	R134a	Ocelový Plech
S101046G031	1000W	3400Btu/h	460V	1	R134a	Ocelový Plech
S101546G031	1500W	5000Btu/h	460V	3	R134a	Ocelový Plech
S162546G031	2500W	8500Btu/h	460V	3	R134a	Ocelový Plech
S162046G031	2000W	6800Btu/h	460V	3	R134a	Ocelový Plech
S164046G031	4000W	13500Btu/h	460V	3	R134a	Ocelový Plech

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE