

# Beam Attachment Kit



## FUNKTIONER

For installations where the cable cannot be looped around the steel beam

Can support two catenary systems using each eye nut as an anchoring point

Kit includes beam clamps and eye nuts

Installs on top or bottom flange of I-beams or bar joists

## SPECIFIKATIONER

Table 1/2


| Katalognummer | Artikelnummer | Material | Finish                                | Flange Thickness (FT) | Rod Size (RS) | Static Load 1 (F1) |
|---------------|---------------|----------|---------------------------------------|-----------------------|---------------|--------------------|
| SLBM12        | 196852        | Stål     | Electrogalvanized, Hot-Dip Galvanized | 10 - 20 mm            | 12            | 400N               |

Table 2/2

| Katalognummer | Artikelnummer | Static Load 2 (F2) | Static Load 3 (F3) |
|---------------|---------------|--------------------|--------------------|
| SLBM12        | 196852        | 700N               | 800N               |

## YDERLIGERE PRODUKTOPLYSNINGER

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

