


# Panhead Screw, Pozidriv



Good compromise between profile height and bearing area. Better load distribution than round heads. Compatible with automated assembly.

## VLASTNOSTI

Phillips screw offers a high level of torque to achieve quick and easy installation. The Phillips screw drive is more stable with the help of four contact points and better performing with screwdrivers. But unlike other kinds of screw drives, the Phillips drive is designed to cam out in which screw drive slips out of the cross head once the torque is needed to drive the screw exceeds a certain amount to avoid over tightening.

Pozidriv has a set of 45° radial indentations from the main cross recess leading to 4 additional contact points and greater stabilization to provide a greater contact surface. As a result, it decrease cam-out and wear, which allows greater torque to be applied.

**Product Type:** Screw  
**Materiál:** Ocel



## SPECIFIKACE

Table 1/2

| Katalogové číslo | Diameter | Length | Povrchová úprava | Množství v balení | Thread Size | Produktová řada                                                                             |
|------------------|----------|--------|------------------|-------------------|-------------|---------------------------------------------------------------------------------------------|
| 21102-024        | 3mm      | 6mm    | Pozinkovaná Ocel | 100               | M3          |                                                                                             |
| 21120-150        | 5mm      | 10mm   | Pozinkovaná Ocel | 100               | M5          |                                                                                             |
| 21101-314        |          | 5mm    | Nickel Plated    | 100               | M2.5        |                                                                                             |
| 21100-022        | 6mm      | 16mm   | Pozinkovaná Ocel | 100               | M6          | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO |
| 21120-203        | 6mm      | 16mm   | Pozinkovaná Ocel | 100               | M6          |                                                                                             |

| Katalogové číslo | Diameter | Length | Povrchová úprava | Množství v balení | Thread Size | Produktová řada                                                                             |
|------------------|----------|--------|------------------|-------------------|-------------|---------------------------------------------------------------------------------------------|
| 21100-021        | 6mm      | 16mm   | Pozinkovaná Ocel | 50                | M6          | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO |
| 21120-202        | 6mm      | 16mm   | Pozinkovaná Ocel | 50                | M6          |                                                                                             |
| 21100-650        | 6mm      | 16mm   | Pozinkovaná Ocel | 100               | M6          | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO |
| 21101-219        |          | 6mm    | Nickel Plated    | 100               | M2.5        | Frame Type Plug-In Unit                                                                     |
| 21101-069        |          | 8mm    | Nickel Plated    | 100               | M2.5        | Frame Type Plug-In Unit                                                                     |
| 21101-220        |          | 10mm   | Nickel Plated    | 100               | M2.5        | Frame Type Plug-In Unit                                                                     |
| 21101-221        |          | 12mm   | Nickel Plated    | 100               | M2.5        | Frame Type Plug-In Unit                                                                     |
| 21100-788        |          | 12mm   | Pozinkovaná Ocel | 100               | M5          | EuropacPRO                                                                                  |
| 21101-222        |          | 16mm   | Nickel Plated    | 100               | M2.5        | Frame Type Plug-In Unit                                                                     |

Table 2/2

| Katalogové číslo | Typ           | Works With                                              | Thread Type | Certifications |
|------------------|---------------|---------------------------------------------------------|-------------|----------------|
| 21102-024        | Panhead Screw |                                                         | Metric      | RoHS           |
| 21120-150        | Coding Block  | Cabinet                                                 |             | RoHS           |
| 21101-314        | Panhead Screw | Backplanes, Test Adapters                               |             | RoHS           |
| 21100-022        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP |             | RoHS           |
| 21120-203        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP |             |                |
| 21100-021        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP |             | RoHS           |
| 21120-202        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP |             |                |
| 21100-650        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP |             | RoHS           |
| 21101-219        | Panhead Screw | Backplanes, Test Adapters                               |             | RoHS           |
| 21101-069        | Panhead Screw | Backplanes, Test Adapters                               |             | RoHS           |
| 21101-220        | Panhead Screw | Backplanes, Test Adapters                               |             | RoHS           |
| 21101-221        | Panhead Screw | Backplanes, Test Adapters                               |             | RoHS           |
| 21100-788        | Panhead Screw | Subracks                                                |             | RoHS           |
| 21101-222        | Panhead Screw | Backplanes, Test Adapters                               |             | RoHS           |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**