

nVent CADDY Speed Link Catenary Kit, 30 m Length

KATALOGNUMMER

SLK6L30

FUNKTIONER

Kit includes precut length of fuse-cut cable to avoid fraying, pre-assembled hook end fitting and tool-free locking device to save installation time

Fastens to the building structure by looping around and hooking to wire rope

Hook end-fitting easily attaches to eye nut

Spring latch helps provide secure connection



PRODUKTEGENSKABER

Artikelnummer: 196805

Materiale: Stål;Zinc Alloy;Polypropylene

Finish: Electrogalvanized;Hot-Dip Galvanized

Wire Rope Diameter: 6 mm

Wire Rope Length: 30m

A: 75 mm

B: 40 mm

C: 15 mm

Height (H): 108 mm

Width (W): 41 mm

Thickness (T): 30 mm

Angle (a): 60 ° Max

YDERLIGERE PRODUKTOPLYSNINGER


Wire Rope Length is measured from the end of the wire rope to the hook side of the swage.

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

Horizontal Intallation		
Preload	1000 N	450 N
Static Load 1 (F1)	490 N	590 N
Static Load 2 (F2)	880 N	1080 N
Static Load 3 (F3)	980 N	1180 N
Vertical Installation		
Static Load 4 (F4)	4440 N	

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

