

Flanged Drop-in Anchor



FUNKTIONER

Internal thread provides easy removal and serviceability

Installs flush for standard embedment

Suitable for redundant non-structural systems on cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

Lip makes the flush installation easier by helping achieve consistent anchor depth and easy threaded rod alignment

Materiale: Stål
Finish: Electrogalvanized



SPECIFIKATIONER

Katalognummer	Artikelnummer	Hole Size (HS)	Length (L)	Drill Bit Diameter (Ø)	Certificeringer
LAM1040	574420	10 mm	40mm	12 mm	CE, 14-0068, VdS, CE, 14-0135
LAM1250	574430	12 mm	50mm	15 mm	CE, 14-0068, VdS, CE, 14-0135
LAM625	589890	6 mm	25mm	8 mm	CE, 14-0135, CE, 14-0068
LAM830	574410	8 mm	30mm	10 mm	CE, 14-0068, CE, 14-0135, VdS


Characteristic Axial Loads from ETA 14-0135

Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
LAM625	-	2.44 kN	25 mm
LAM830	-	3.21 kN	30 mm
LAM1040	-	4.23 kN	40 mm
LAM1250	-	5.92 kN	50 mm

Characteristic Axial Loads from ETA 14-0068 - for redundant non-structural systems

Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
LAM625	0.80 kN	0.80 kN	25 mm
LAM830	1.20 kN	1.20 kN	30 mm
LAM1040	1.70 kN	1.70 kN	40 mm
LAM1250	2.60 kN	2.60 kN	50 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/CRDDT

