

nVent CADDY Superfix 243 M8



FUNKTIONER

Includes easy closing mechanism

Combo head bolt works with slotted, hex, or Phillips drivers

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

Materiale: Stål;EPDM-SBR Rubber
Finish: Electrogalvanized
Farve: Black
Temperature: -50 to 110 °C



SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)	Thickness (T)
SXE019	400056	15 - 19 mm	10	M8	20 mm	1.5 mm
SXE023	400057	21 - 23 mm	15	M8	20 mm	1.5 mm
SXE028	400058	26 - 28 mm	20	M8	20 mm	1.5 mm
SXE035	400059	32 - 35 mm	25	M8	20 mm	1.5 mm
SXE043	400060	40 - 43 mm	32	M8	20 mm	1.5 mm
SXE052	400062	48 - 52 mm	40	M8	20 mm	1.5 mm
SXE058	589310	54 - 58 mm		M8	20 mm	2 mm
SXE061	589320	57 - 61 mm	50	M8	20 mm	2 mm
SXE014	400055	12 - 14 mm	8	M8	20 mm	1.5 mm


Table 2/2

Katalognummer	Artikelnummer	Screw Diameter (Sc)	Screw Length (L)	Static Load
SXE019	400056	6	27mm	1000N
SXE023	400057	6	27mm	1000N
SXE028	400058	6	27mm	1000N
SXE035	400059	6	27mm	1000N
SXE043	400060	6	32mm	1000N
SXE052	400062	6	32mm	1300N
SXE058	589310	6	32mm	1300N
SXE061	589320	6	32mm	1300N
SXE014	400055	6	27mm	1000N

YDERLIGERE PRODUKTOPLYSNINGER

Lining is EPDM rubber.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

