


Wire Basket Tray PreForm 90 degree Elbow, 50 x 450 mm, Black, Pregalvanized

KATALOGNUMMER

WBTR902X18BA



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FUNKTIONER

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems



PRODUKTEGENSKABER

Materiale: Stål

Finish: Pregalvanized;Polyurethane

Farve: Black

Height (H): 50.8 mm

Width (W): 665.734 mm


Length (L): 665.734mm

Hole Size (HS): 19.05 mm

Radius (R): 94.64mm

Unit Weight: 3.175 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

