

nVent CADDY Speed Link SLK with Nail Gun Bracket



FUNKTIONER

Complete system includes wire, locking device and concrete nail gun insert bracket

Clips onto nozzle of gas or battery-actuated nail guns allowing for hands-off installation at structure or from the floor using a pole

Longer leg angle bracket for tool clearance

Quickly and easily attaches to concrete, steel or composite metal decking

Materiale:	Stål;Zinc Alloy;Polypropylene;Nylon
Finish:	Electrogalvanized
Static Load Safety Factor:	5:1
Complies With:	SMACNA HVAC-DCS
Wire Rope Diameter:	1.5 mm

SPECIFIKATIONER

Katalognummer	Artikelnummer	Wire Rope Length	A	B	Static Load
SLK15L2GBSF	197812	2m	38 mm	25.5 mm	195N
SLK15L3GBSF	197813	3m	38 mm	25.5 mm	195N


Height (H):	55 mm
Width (W):	19 mm
Thickness (T):	12.5 mm
Angle (a):	90 ° Max

YDERLIGERE PRODUKTOPLYSNINGER

Static Load represents the static load of the nail gun insert assembly. Please consult with the nail manufacturer to evaluate the static load of the nail and type of concrete used for the installation. Maximum load is the lesser of the static load from the nail manufacturer or the published load for the assembly.

Nail gun insert is compatible with BeA® CN60-688ES, Hilti® BX 3, GX 3, DEWALT® Trak-It C3, SPIT® PULSA 40E, 800E, 700, 1000 or equivalent nailers.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

