

Threaded Coupler for Copper-Bonded Ground Rod, Threaded



The nVent ERICO Sectional Coupler for Copper-Bonded Ground Rod, Threaded is designed to join threaded copper-bonded ground rods while maintaining a durable electrical connection. High-strength couplings are threaded and chamfered at both ends to support easy driving, while the corrosion-resistant construction helps ensure a permanent, low-resistance copper-to-copper connection for grounding applications.

FUNKTIONER

Part of the Color Smart Ground Rod System

High-strength coupling design for joining threaded copper-bonded ground rods

Threaded and chamfered at both ends for easy driving

Corrosion-resistant construction for long-term performance

Provides a permanent copper-to-copper connection

Delivers a low-resistance electrical connection



SPECIFIKATIONER

Table 1/2


Katalognummer	Artikelnummer	Materiale	Ground Rod Diameter, Nominal	Length (L)	Thread Size (TS)	Unit Weight
CR100		Silicon Bronze	1"	99.1mm	1" UNC	0.35 kg
CR58	158040	Bronze	5/8"	61mm	5/8" UNC	0.09 kg

Katalognummer	Artikelnummer	Materiale	Ground Rod Diameter, Nominal	Length(L)	Thread Size (TS)	UnitWeight
SC34	158050	Bronze	3/4"	71mm	3/4" UNC	0.17 kg
CR34		Bronze	3/4"	76.2mm	3/4" UNC	0.15 kg

Table 2/2

Katalognummer	Artikelnummer	Complies With	Certificeringer
CR100		EN IEC 62561-2	cUL, UL
CR58	158040	EN IEC 62561-2	UL, cUL, CSA-US, RUS, CSA
SC34	158050	IEC® EN 62561-2	
CR34			RUS, CSA-US, UL, cUL, CSA

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

