

MDRCPT-2 Manual Din Rail Cutting and Punching Tool



FUNKTIONER

Punches slots and cuts DIN rail without burrs or deformation

Punches horizontal and vertical slots

Works with five different types of DIN rail and M6 threaded rod

Includes ruler, guide and end stops

RoHS compliant



SPECIFIKATIONER

Katalognummer	Artikelnummer	Materiale	Slot Size	Dybde	Height	Length	Unit Weight
MDRCPT-2	559142	Aluminium, Stål	6.5 x 9.5 mm	165mm	200 mm	100mm	13 kg

YDERLIGERE PRODUKTOPLYSNINGER

Horizontal slots must be punched a minimum of 8 mm (0.315") from the edge of the DIN rail. Vertical slots must be punched a minimum of 12 mm (0.472") from the edge of the DIN rail.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE