

Varmeenheder til farlige lokationer, DAHHL



Konstrueret til brug på farlige områder, hvor elektroniske komponenter kræver beskyttelse mod kulde og minusgrader, kondens og korrosion.

INDUSTRISTANDARDE

ATEX, IECEx

II2G Ex d IIC T3 / II2 D Ex Td A21 IP65 T200 C

NEC CSA us

Class I, Div 1 Groups A, B, C, D / Class II Div 1 Groups E, F, G

FUNKTIONER

50W, 80W, 200W, 300W, 400W and 600W models available

Provides freeze protection down to -76 F / -60 C

Conductive and Convection heating types available

50W and 80W models can be mounted directly to manifolds, measuring or analyzing instruments, control valves, and similar equipment

200W, 300W, 400W, 600W models are finned heaters that heat the area by transferring the heat from the heater to surrounding air, creating a convection current

Two thermostat options available with a 50 F / 10 C or 68 F / 20 C set point

Materiale: Aluminium

Finish: Anodized

Farve: Black

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Nominel spænding	Heating Capacity	Spænding AC
HLTSTAT10C	28mm	23mm	109mm			
HLTSTAT20C	28mm	23mm	109mm			
DAHHL501AC	89mm	41mm	30mm	115V	50W	110V
DAHHL801AC	89mm	41mm	30mm	115V	80W	110V

Katalognummer	Højde	Bredde	Dybde	Nominel spænding	Heating Capacity	Spænding AC
DAHHL4001A	226mm	229mm	61mm	115V	400W	110V
DAHHL6001A	325mm	229mm	61mm	115V	600W	110V
DAHHL6002A	325mm	229mm	61mm	220V	600W	207V
DAHHL4002A	226mm	229mm	61mm	220V	400W	207V
DAHHL300AC	325mm	229mm	61mm	115V	300W	110V
DAHHL200AC	226mm	229mm	61mm	115V	200W	110V

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE