

# Hultætninger af metal

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals . Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.



## INDUSTRISTANDARDER

UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)

Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66

## FUNKTIONER

Oliebestandig pakning medfølger

Available in multiple colors and sizes

Steel model has plated stud (10-32x5/8) and wing nut

Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

## SPECIFIKATIONER

Table 1/2

| Katalognummer | Materiale           | Finish                | Farve | Farvekode | Tykkelse | Hole Diameter |
|---------------|---------------------|-----------------------|-------|-----------|----------|---------------|
| AS056MSS      | Stainless Steel 304 | Polished              |       |           | 1.5mm    | 14mm max      |
| AS056M        | Lakeret Stål        | Struktur Pulvermaling | Gray  | ANSI 61   | 1.5mm    | 14mm max      |
| AS056MFB      | Lakeret Stål        | Struktur Pulvermaling | Gray  | ANSI 61   | 1.5mm    | 14mm max      |

| Katalognummer | Materiale           | Finish                | Farve      | Farvekode | Tykkelse | Hole Diameter |
|---------------|---------------------|-----------------------|------------|-----------|----------|---------------|
| AS056MLG      | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 14mm max      |
| AS056CB       | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 14mm max      |
| ASPBGSS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 22mm max      |
| ASPBG         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 22mm max      |
| AS100LG       | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 35mm          |
| AS100SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 35mm          |
| AS100         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 35mm          |
| AS050         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 22mm max      |
| AS050LG       | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 22mm max      |
| AS050SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 22mm max      |
| AS350SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 105mm max     |
| AS250SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 76mm max      |
| AS125LG       | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 43mm max      |
| AS150SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 51mm max      |
| AS400SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 117mm max     |
| AS125SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 43mm max      |
| AS075         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 27mm max      |

Table 2/2

| Katalognummer | Materiale           | Finish                | Farve      | Farvekode | Tykkelse | Hole Diameter |
|---------------|---------------------|-----------------------|------------|-----------|----------|---------------|
| AS150LG       | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 51mm max      |
| ASPB          | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 32mm max      |
| AS300SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 92mm max      |
| AS300         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 92mm max      |
| AS150         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 51mm max      |
| AS125         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 43mm max      |
| AS400         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 117mm max     |
| AS200         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 64mm max      |
| ASPBSS        | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 32mm max      |
| AS200SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 64mm max      |
| AS250         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 76mm max      |
| AS075SS       | Stainless Steel 304 | Polished              |            |           | 1.5mm    | 27mm max      |
| ASPB LG       | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 32mm max      |
| AS350         | Lakeret Stål        | Struktur Pulvermaling | Gray       | ANSI 61   | 1.5mm    | 105mm max     |
| AS200LG       | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 64mm max      |
| AS075LG       | Lakeret Stål        | Struktur Pulvermaling | Light Gray | RAL 7035  | 1.5mm    | 27mm max      |

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**