


Slim Fit indendørs køleenhed



SpectraCool SlimFit Air Conditioners are designed with three space-saving mounting options to maximize footprint. They have been developed to meet the requirements of worldwide industrial customers, easy to specify and easy to use. From filterless operation to global certifications, the SpectraCool Slim Fit Air Conditioner makes automation cooling easy for system designers and operations maintenance teams around the world.

Select units come with a Commboard for Remote Access Control (RAC), an integrated, parametric controller designed to work seamlessly with our enclosure air conditioner units for the purpose of remotely monitoring and managing anywhere from a single unit to an entire network of Spectra cool air conditioners from virtually anywhere in the world with a secure internet connection. Ensure that your systems are always running at optimal temperature levels, increase productivity and improve overall system reliability.

INDUSTRISTANDARDE

UL/cUL Listed Type 12; File No.SA6453

CE, EAC, RoHS

Cooling performance tested by TÜV SÜD Germany, according to DIN EN 14511

IP 54 internal loop, IP 34 external loop

FUNKTIONER

Slim Fit-design med tre monteringsmuligheder: fuldt indbygget, delvist indbygget og påmontering

Æstetisk designet plastdæksel, der optimerer luftstrømmen

Driftstemperaturområde fra 50 °F / 10 °C til 131 °F / 55 °C

Nem filterudskiftning til ekstremt støvede miljøer

Støvafvisende varmevekslerer til drift uden filter

Aktiv kondensatstyring for at forhindre vanddryp

Energieffektiv roterende kompressor

Strømindgang via klemrække

Standardudskæringsmål for nem udskiftning

Hver enhed er funktionstestet før afsendelse

Standardklima anlæg er kompatibel med en dørkontakt til kabinettet

Fjernbetjeningsenheder understøtter op til 2 temperatursensorer og 10 alarmer. De understøtter flere kommunikationsprotokoller: SNMP, Modbus TCP, Ethernet/IP og Profinet.

Monteringsbeslag, pakninger og brugervejledning medfølger enheden

Finish: Struktur Pulvermaling
Farve: Light Gray
Farvekode: RAL 7035

SPECIFIKATIONER

Katalognummer	Nominel kapacitet Watt	Nominel kapacitet Btu/t	Nominel spænding	Antal faser	Kølemiddel	Materiale
S060316G031	300W	1000Btu/h	115V	1	R134a	Lakeret Stål
S060326G031	300W	1000Btu/h	230V	1	R134a	Lakeret Stål
S060516G031	500W	1700Btu/h	115V	1	R134a	Lakeret Stål
S060526G031	500W	1700Btu/h	230V	1	R134a	Lakeret Stål
S101016G031	1000W	3400Btu/h	115V	1	R134a	Lakeret Stål
S101026G031	1000W	3400Btu/h	230V	1	R134a	Lakeret Stål
S101046G031	1000W	3400Btu/h	460V	1	R134a	Lakeret Stål
S101516G031	1500W	5000Btu/h	115V	1	R134a	Lakeret Stål
S101526G031	1500W	5000Btu/h	230V	1	R134a	Lakeret Stål
S101546G031	1500W	5000Btu/h	460V	3	R134a	Lakeret Stål
S162026G031	2000W	6800Btu/h	230V	1	R134a	Lakeret Stål
S162046G031	2000W	6800Btu/h	460V	3	R134a	Lakeret Stål
S162526G031	2500W	8500Btu/h	230V	1	R134a	Lakeret Stål
S162546G031	2500W	8500Btu/h	460V	3	R134a	Lakeret Stål
S164046G031	4000W	13500Btu/h	460V	3	R134a	Lakeret Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.