

# Wire Basket Tray PreForm Tee



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## MERKMALE

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Material:** Stahl  
**Oberfläche:** Vorverzinkung; Polyurethan



## SPEZIFIKATIONEN

Table 1/2

| Katalognummer | Farbe   | Höhe (H) | Breite (W) | Länge (L) | Lochgröße (HS) | Radius (R) | Stückgewicht |
|---------------|---------|----------|------------|-----------|----------------|------------|--------------|
| WBTT2X12      |         | 50.8 mm  | 515.62 mm  | 711.2mm   | 19.05 mm       | 94.64mm    | 2.722 kg     |
| WBTT2X12BA    | Schwarz | 50.8 mm  | 515.62 mm  | 711.2mm   | 19.05 mm       | 94.64mm    | 2.722 kg     |
| WBTT2X18      |         | 50.8 mm  | 668.02 mm  | 863.6mm   | 19.05 mm       | 94.64mm    | 4.536 kg     |
| WBTT2X18BA    | Schwarz | 50.8 mm  | 668.02 mm  | 863.6mm   | 19.05 mm       | 94.64mm    | 4.536 kg     |

| Katalognummer | Farbe   | Höhe (H)              | Breite (W) | Länge (L)  | Lochgröße (HS) | Radius(R) | Stückgewicht |
|---------------|---------|-----------------------|------------|------------|----------------|-----------|--------------|
| WBTT2X24      |         | 50.8 mm               | 817.88 mm  | 1013.46m m | 19.05 mm       | 94.64mm   | 7.257 kg     |
| WBTT2X24BA    | Schwarz | 50.8 mm               | 817.88 mm  | 1013.46m m | 19.05 mm       | 94.64mm   | 7.257 kg     |
| WBTT2X4       |         | 50.8 mm               | 317.5 mm   | 513.08mm   |                | 94.64mm   | 0.454 kg     |
| WBTT2X4BA     | Schwarz | 50.8 mm               | 317.5 mm   | 513.08mm   |                | 94.64mm   | 0.454 kg     |
| WBTT2X6       |         | 50.8 mm               | 365.76 mm  | 561.34mm   |                | 94.64mm   | 1.361 kg     |
| WBTT2X6BA     | Schwarz | 50.8 mm               | 365.76 mm  | 561.34mm   |                | 94.64mm   | 1.361 kg     |
| WBTT2X8       |         | 50.8 mm               | 416.56 mm  | 612.14mm   |                | 94.64mm   | 1.814 kg     |
| WBTT2X8BA     | Schwarz | 50.8 mm               | 416.56 mm  | 612.14mm   |                | 94.64mm   | 1.814 kg     |
| WBTT6X6       |         | 152.39999999999998 mm |            |            |                |           |              |
| WBTT2X4S4     |         | 50.8 mm               |            |            |                |           |              |
| WBTT4X12      |         | 101.6 mm              |            |            |                |           |              |
| WBTT4X12BA    | Schwarz | 101.6 mm              |            |            |                |           |              |
| WBTT4X18      |         | 101.6 mm              |            |            |                |           |              |
| WBTT4X18BA    | Schwarz | 101.6 mm              |            |            |                |           |              |
| WBTT4X24      |         | 101.6 mm              |            |            |                |           |              |
| WBTT4X24BA    | Schwarz | 101.6 mm              |            |            |                |           |              |

Table 2/2

| Katalognummer | Farbe   | Höhe (H) | Breite (W) | Länge (L) | Lochgröße (HS) | Radius (R) | Stückgewicht |
|---------------|---------|----------|------------|-----------|----------------|------------|--------------|
| WBTT4X4       |         | 101.6 mm |            |           |                |            |              |
| WBTT4X4BA     | Schwarz | 101.6 mm |            |           |                |            |              |
| WBTT4X6       |         | 101.6 mm |            |           |                |            |              |
| WBTT4X6BA     | Schwarz | 101.6 mm |            |           |                |            |              |
| WBTT6X12      |         | 152.4 mm |            |           |                |            |              |
| WBTT6X12BA    | Schwarz | 152.4 mm |            |           |                |            |              |
| WBTT6X18      |         | 152.4 mm |            |           |                |            |              |
| WBTT6X18BA    | Schwarz | 152.4 mm |            |           |                |            |              |
| WBTT6X24      |         | 152.4 mm |            |           |                |            |              |

| Katalognummer | Farbe   | Höhe (H) | Breite (W) | Länge (L) | Lochgröße (HS) | Radius (R) | Stückgewicht |
|---------------|---------|----------|------------|-----------|----------------|------------|--------------|
| WBTT6X24BA    | Schwarz | 152.4 mm |            |           |                |            |              |
| WBTT6X36      |         | 152.4 mm |            |           |                |            |              |

## DIAGRAMME

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

### Nordamerika

+1.800.753.9221  
Option 1 – Kundendienst  
Option 2 – Technischer  
Support

### Europa

Niederlande:  
+31 800-0200135  
Frankreich:  
+33 800 901 793

### Europa

Deutschland:  
800 1890272  
Sonstige Länder:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

