


# Teleskop-Dosenwinkel. 400–635 mm Ständerabst., 38mm 54mm 63,5 mm Anschl.- Dosen.

## KATALOGNUMMER

**TSGB1624**



The nVent CADDY Telescoping Screw Gun Box Bracket, First Means is a simple and intuitive support for mounting electrical boxes within stud wall applications. This solution delivers both traditional and retrofit mounting, which allows the bracket to bend for multiple depths and mount from both the front and back of the stud—making it ideal for when drywall has already been installed. As the first means of support, conduit can be run directly to the electrical box while ensuring a smooth, flat drywall finish with side-mount installations. The notched and clearly marked bend points make installation safe, fast and easy.

## MERKMALE

Designed for both single and multiple box mounting

Unique single-component break-apart design

Stamped inch markings and pilot holes accelerate precise box conduit mounting

Pilot holes allow for easy access with a screwdriver

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly



## PRODUKTMERKMALE

Artikelnummer: 187199

Material: Stahl

Oberfläche: Vorverzinkung

Bolzenabstand: 400 - 635 mm

## WARNUNG

---

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

### Nordamerika

+1.800.753.9221  
Option 1 – Kundendienst  
Option 2 – Technischer  
Support

### Europa

Niederlande:  
+31 800-0200135  
Frankreich:  
+33 800 901 793

### Europa

Deutschland:  
800 1890272  
Sonstige Länder:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

