


# Steel Flange Adapter



This code-compliant Structural Attachment is part of the nVent CADDY line of innovative rigid bracing system, designed to provide superior performance and meet the highest seismic load requirements. Its innovative design allows quick and easy installation onto both top or bottom flange of a wide range of steel I-Beams. Its snap-off bolts make inspection of seismic sway braces simple.

## FEATURES

Installs on top or bottom flange of I-beams or bar joists

Low profile easily fits between metal deck and steel structure

Thumb spring retainer allows for ease of positioning

Available pre-assembled to the Universal Structural Bracket, eliminating field assembly

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

Meets NFPA® 13 as pre-qualified for seismic applications

FM® Specification Tested

**Material:** Steel  
**Finish:** Electrogalvanized



## SPECIFICATIONS

| Catalog Number | Flange Thickness (FT) | A     | B     | C     | D     |
|----------------|-----------------------|-------|-------|-------|-------|
| CSBS1N         | 6 - 19 mm             | 21 mm | 23 mm | 92 mm | 67 mm |
| CSBS2N         | 19 - 31 mm            | 23 mm | 23 mm | 92 mm | 79 mm |

ADDITIONAL PRODUCT DETAILS

Structure Attachment and Brace Member are not included.

| UL Loads    |                              |                  |                         |             |
|-------------|------------------------------|------------------|-------------------------|-------------|
| Part Number | Structure Attachment Fitting | Flange Thickness | Brace Member            | Load Rating |
| CSBS1xxx    | CSBU1xxx                     | 6 - 8 mm         | DN25 - DN50 Sch. 40 NPS | 6672 N      |
|             |                              | 8 - 19 mm        |                         | 7561 N      |
|             | CSBURC12                     | 6 - 19 mm        | CSB12CBL                | 1859 N      |
|             |                              |                  | CSB18CBL                | 3434 N      |
|             |                              |                  | CSB36CBL                | 4893 N      |
| CSBS2xxx    | CSBU1xxx                     | 19 - 31 mm       | DN25 - DN50 Sch. 40 NPS | 7561 N      |
|             | CSBURC12                     | 19- 31 mm        | CSB12CBL                | 1859 N      |
|             |                              |                  | CSB18CBL                | 3434 N      |
|             |                              |                  | CSB36CBL                | 4893 N      |
|             |                              |                  |                         |             |

| FM Loads    |                                                          |          |          |          |                       |          |          |          |
|-------------|----------------------------------------------------------|----------|----------|----------|-----------------------|----------|----------|----------|
| Part Number | Horizontal Capacity per Installation Angle from Vertical |          |          |          |                       |          |          |          |
|             | Perpendicular to Structure                               |          |          |          | Parallel to Structure |          |          |          |
|             | 30°- 44°                                                 | 45°- 59° | 60°- 74° | 75°- 90° | 30°- 44°              | 45°- 59° | 60°- 74° | 75°- 90° |
| CSBS1xxx    | 3780 N                                                   | 7910 N   | 12320 N  | 12630 N  | 3910 N                | 6360 N   | 8980 N   | 10720 N  |
| CSBS2xxx    | 5420 N                                                   | 9510 N   | 11470 N  | 12760 N  | 4890 N                | 8090 N   | 9740 N   | 11920 N  |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

