

# Improved nVent CADDY Cat HP J-Hook



nVent CADDY Cat HP J-Hooks are the foundation of the nVent CADDY Cat HP System. The revamped nVent CADDY Cat HP J-Hook offers contractors three unique, UL-certified attachment methods out of the box—wall, ceiling, and threaded rod installations. This added functionality enables contractors to reduce SKU inventory while maintaining efficiency and continued progress on the jobsite with the most common structural attachment methods.

The modernized design of the nVent CADDY Cat HP J-Hook is engineered to provide optimal support and protection for today's rapidly evolving, high-performing low voltage cable. Contractors can feel confident utilizing the nVent CADDY Cat HP J-Hook due to its installation versatility, superior cable support and protection, and technical certifications.

## FEATURES

One through-hole for easier installation of threaded rod

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material | Finish        | Diameter (Ø) | Area                | Cable Capacity, Cat 5e |
|----------------|----------------|----------|---------------|--------------|---------------------|------------------------|
| CAT16HP        | 181061         | Steel    | Pregalvanized | 25 mm        | 690mm <sup>2</sup>  | 20                     |
| CAT21HP        | 181188         | Steel    | Pregalvanized | 33.3 mm      | 1174mm <sup>2</sup> | 50                     |
| CAT48HP        | 181063         | Steel    | Pregalvanized | 75 mm        | 5974mm <sup>2</sup> | 200                    |
| CAT64HP        | 181064         | Steel    | Pregalvanized | 100 mm       | 9987mm <sup>2</sup> | 330                    |
| CAT32HP        | 181062         | Steel    | Pregalvanized | 50 mm        | 2561mm <sup>2</sup> | 90                     |

Table 2/2




| Catalog Number | Article Number | Cable Capacity, Cat 6 | Cable Capacity, Cat 6A | Height 1 (H1) | Height 2 (H2) | Static Load |
|----------------|----------------|-----------------------|------------------------|---------------|---------------|-------------|
| CAT16HP        | 181061         | 15                    | 10                     | 108.9mm       | 90.2mm        | 267N        |
| CAT21HP        | 181188         | 40                    | 25                     | 122.2mm       | 103.6mm       | 267N        |
| CAT48HP        | 181063         | 150                   | 80                     | 164.6mm       | 148.8mm       | 267N        |
| CAT64HP        | 181064         | 220                   | 140                    | 188.5mm       | 180mm         | 267N        |
| CAT32HP        | 181062         | 60                    | 35                     | 130.8mm       | 112.3mm       | 267N        |

## ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

