

Speedway Cable Ladder, 750 mm x 110 mm x 3 m

CATALOG NUMBER

CL110X750HD



The SPEEDWAY Cable Ladder is the backbone of the SPEEDWAY Cable Ladder System. Highly engineered features help ensure a secure installation that complies with industry codes and standards for high-performance cables. The cable ladder is designed to efficiently accommodate field transitions utilizing the SPEEDLOK integrated coupling systems.

FEATURES

- Provides optimal support for high-performance low voltage and data cables
- Easy cable ladder transitions with innovative SPEEDLOK integrated coupling system
- Safety edge protects cables during installation
- Slotted side channel, eliminating field drilling for cut-to-length applications
- IEC 61537 load rating and earthing compliant
- Responsive design and layout services, including seismic




PRODUCT ATTRIBUTES

- Article Number: 840040
- Material: Steel
- Finish: Hot-Dip Galvanized
- Width (W): 750 mm
- Height (H): 110 mm
- A: 25 mm

B: 85 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/CA001

