

# Quick Grip Jr. Lateral Sway Brace



## FEATURES

Easy two-step installation eliminates extra trips between structure and service pipe

Works with 1" and 1 1/4" (25 mm and 32 mm) brace pipes to reduce inventory

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

**Material:** Steel  
**Finish:** Electrogalvanized





## SPECIFICATIONS

| Catalog Number | Article Number | NB/DN | Height (H) | Width (W) |
|----------------|----------------|-------|------------|-----------|
| CSBQIKCL0100EG | 404373         | 25    | 130.2 mm   | 65.3 mm   |
| CSBQIKCL0125EG | 404374         | 32    | 136.5 mm   | 74.4 mm   |
| CSBQIKCL0150EG | 404375         | 40    | 142.9 mm   | 80.2 mm   |
| CSBQIKCL0200EG | 404376         | 50    | 161.9 mm   | 92.3 mm   |

| UL Loads (Listed for Restraints) |                       |                  |                  |
|----------------------------------|-----------------------|------------------|------------------|
| Part Number                      | Service Pipe Schedule | Lateral          |                  |
|                                  |                       | 25 mm Brace Pipe | 32 mm Brace Pipe |
| CSBQIKCL0100EG                   | EN 10255 L            | N/A              | N/A              |
|                                  | EN 10255 M            | 2910 N           | 2910 N           |
|                                  | EN 10255 H            | 2910 N           | 2910 N           |
| CSBQIKCL0125EG                   | EN 10255 L            | 2910 N           | 2400 N           |
|                                  | EN 10255 M            | 2910 N           | 2400 N           |
|                                  | EN 10255 H            | 2910 N           | 2400 N           |
| CSBQIKCL0150EG                   | EN 10255 L            | 3330 N           | 2910 N           |
|                                  | EN 10255 M            | 3330 N           | 2910 N           |
|                                  | EN 10255 H            | 3330 N           | 2910 N           |
| CSBQIKCL0200EG                   | EN 10255 L            | 3330 N           | 2400 N           |
|                                  | EN 10255 M            | 3330 N           | 2400 N           |
|                                  | EN 10255 H            | 3330 N           | 2400 N           |

| FM Loads       |                       |                                                          |          |          |          |
|----------------|-----------------------|----------------------------------------------------------|----------|----------|----------|
| Part Number    | Service Pipe Schedule | Lateral                                                  |          |          |          |
|                |                       | Horizontal Capacity per Installation Angle from Vertical |          |          |          |
|                |                       | 30°- 44°                                                 | 45°- 59° | 60°- 74° | 75°- 90° |
| CSBQIKCL0100EG | EN10255 L (Lightwall) | 1290 N                                                   | 1830 N   | 2200 N   | 2445 N   |
|                | EN10255 M (10)        | 665 N                                                    | 935 N    | 1245 N   | 1400 N   |
|                | EN10255 H (40)        | 2115 N                                                   | 2960 N   | 3670 N   | 4115 N   |
| CSBQIKCL0125EG | EN10255 L (Lightwall) | 1290 N                                                   | 1830 N   | 2200 N   | 2445 N   |
|                | EN10255 M (10)        | 665 N                                                    | 935 N    | 1245 N   | 1400 N   |
|                | EN10255 H (40)        | 2115 N                                                   | 2960 N   | 3670 N   | 4115 N   |
| CSBQIKCL0150EG | EN10255 L (Lightwall) | 1290 N                                                   | 1830 N   | 2200 N   | 2445 N   |
|                | EN10255 M (10)        | 665 N                                                    | 935 N    | 1245 N   | 1400 N   |
|                | EN10255 H (40)        | 2115 N                                                   | 2960 N   | 3670 N   | 4115 N   |
| CSBQIKCL0200EG | EN10255 L (Lightwall) | 1735 N                                                   | 2445 N   | 2980 N   | 3335 N   |
|                | EN10255 M (10)        | 1555 N                                                   | 2225 N   | 2760 N   | 3070 N   |
|                | EN10255 H (40)        | 2180 N                                                   | 3070 N   | 3780 N   | 4225 N   |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

