

nVent CADDY Speed Link SLS with Wedge Anchor, 2 mm Wire, 3 m Length



CATALOG NUMBER

SLS2L3WA6

FEATURES

Complete system includes wire, locking device and wedge anchor from Powers Fasteners, Inc.

Quickly and easily attaches into cracked and non-cracked concrete

Installs in strut profiles without the need to insert fingers or tools into the strut

Finger tightening of nut secures the locking device into position without tools

No special tools required

ETA-13/0355 assessment available for wedge anchor from Powers Fasteners, Inc



PRODUCT ATTRIBUTES

Article Number: 196759

Material: Steel;Polypropylene;Zinc Alloy

Finish: Electrogalvanized

Static Load Safety Factor: 5:1

Complies With: SMACNA HVAC-DCS

Wire Rope Diameter: 2 mm

Wire Rope Length: 3m

Length (L): 63.5mm

Drill Bit Diameter: 6mm

Drill Hole Depth: 60mm

Embedment Depth: 55 mm Min

Static Load: 270N

Thread Size (TS): M8

Height 1 (H1): 53mm

Height 2 (H2): 43.5mm

Width (W): 16 mm

Thickness (T): 4 mm Max

Hole Size (HS): 8 - 10 mm

Slot Size (SS): 8 x 6.5 mm - 8 x 10 mm

ADDITIONAL PRODUCT DETAILS

The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

Total load per wire on a multi-tier trapeze must not exceed static load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

