

# Multi Attachment



## FEATURES

Disperses load over two anchors

Minimizes the number of installed braces needed for concrete and wood structures

Ideal for deck installations

Use for both lateral and longitudinal sway brace applications

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

**Material:** Steel  
**Finish:** Electrogalvanized



## SPECIFICATIONS

| Catalog Number | Article Number | Hole Size 1 (HS1) | Hole Size 2 (HS2) | A        | B       | C       | D        |
|----------------|----------------|-------------------|-------------------|----------|---------|---------|----------|
| CSBMA050050EG  | 404371         | 14 mm             | 14 mm             | 304.8 mm | 63.5 mm | 63.5 mm | 228.6 mm |
| CSBMA050075EG  | 404372         | 20 mm             | 14 mm             | 304.8 mm | 63.5 mm | 63.5 mm | 228.6 mm |


## ADDITIONAL PRODUCT DETAILS

Mount to structure using holes indicated in HS1.

Structure Attachment and Brace Member are not included.

| FM Loads      |                                                          |           |           |           |
|---------------|----------------------------------------------------------|-----------|-----------|-----------|
| Part Number   | Horizontal Capacity per Installation Angle from Vertical |           |           |           |
|               | 30° - 44°                                                | 45° - 59° | 60° - 74° | 75° - 90° |
| CSBMA050050EG | 14,630 N                                                 | 20,100 N  | 24,640 N  | 27,570 N  |
| CSBMA050075EG | 14,630 N                                                 | 20,100 N  | 24,640 N  | 27,570 N  |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

