

Copper-Bonded Ground Rod, Threaded



FEATURES

Cold-rolled threads with continuous, unbroken grain flows preserve copper coating and are stronger than cut threads

99.9% pure electrolytic copper coating

Rods have a high carbon steel core and tip that provide superior strength when driving

Copper coating will not crack when bent or tear when driven

Minimum copper coating of 10 mils on rods listed to UL® 467

nVent ERICO name, length, diameter and part number is roll-stamped within 12" (304,8 mm) of chamfered end

UL logo and control number where applicable stamped on each rod for easy inspection after installation

Material: Copper-Bonded Steel
Tensile Strength: 552 MPa Min



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Color	Thread Location	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)
625850	625850	Silver	Chamfered (Non-Pointed) End Only	5/8"	14.2 mm	5/8" UNC
631300		Green	Pointed and Chamfered Ends	1/2"	12.8 mm	9/16" UNC
631303		Green	Pointed and Chamfered Ends	1/2"	12.8 mm	9/16" UNC
631340		Green	Pointed and Chamfered Ends	1/2"	12.8 mm	9/16" UNC
631350		Green	Pointed and Chamfered Ends	1/2"	12.8 mm	9/16" UNC
631360		Green	Pointed and Chamfered Ends	1/2"	12.8 mm	9/16" UNC

Catalog Number	Article Number	Color	Thread Location	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)
631380		Green	Pointed and Chamfered Ends	1/2"	12.8 mm	9/16" UNC
633400		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633400ESB			Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633403		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633415		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633430		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
6334330		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633440		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633450		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633460		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633463		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633470		Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633480	633480	Yellow	Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC
633480ESB			Pointed and Chamfered Ends	3/4"	17.3 mm	3/4" UNC

Table 2/2

Catalog Number	Article Number	Color	Thread Location	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)
634400			Pointed and Chamfered Ends	1"	23.2 mm	1" UNC
635800		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635800ESB			Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635803		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC

Catalog Number	Article Number	Color	Thread Location	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)
635830		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635840		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635843		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635850		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635860		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
6358660		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635870		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635880	635880	Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635880ESB			Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC
635883		Silver	Pointed and Chamfered Ends	5/8"	14.2 mm	5/8" UNC

Table 1/2

Catalog Number	Article Number	Length (L)	Plating Thickness	Unit Weight	Complies With	Certifications
625850	625850	1.5m	254µm	1.9 kg	IEC® EN 62561-2	
631300		3m	254µm	3.1 kg	ANSI®/NEMA® GR1	CSA-US, CSA, UL, cUL
631303		3m	330µm	3.2 kg	ANSI®/NEMA® GR1	cUL, UL
631340		1.2m	254µm	1.2 kg		
631350		1.5m	254µm	1.6 kg		
631360		1.8m	254µm	1.9 kg		
631380		2.4m	254µm	2.4 kg	ANSI®/NEMA® GR1	UL
633400		3m	254µm	5.7 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	UL, cUL, RUS, CSA-US, CSA
633400ESB		3m	254µm	5.7 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	
633403		3m	330µm	5.7 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	cUL, UL

Catalog Number	Article Number	Length (L)	Plating Thickness	Unit Weight	Complies With	Certifications
633415		4.6m	254µm	8.5 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	UL, cUL
633430		0.9m	254µm	1.7 kg	IEC® EN 62561-2	
6334330		1m	254µm	2.79 kg	IEC® EN 62561-2	
633440		1.2m	254µm	2.2 kg	IEC® EN 62561-2	
633450		1.5m	254µm	2.8 kg	IEC® EN 62561-2	
633460		1.8m	254µm	3.2 kg	IEC® EN 62561-2	
633463		1.8m	330µm	3.2 kg	IEC® EN 62561-2	
633470		2.1m	254µm	3.9 kg	IEC® EN 62561-2	
633480	633480	2.4m	254µm	4.4 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	UL, RUS
633480ESB		2.4m	254µm	4.4 kg	IEC® EN 62561-2	

Table 2/2


Catalog Number	Article Number	Length (L)	Plating Thickness	Unit Weight	Complies With	Certifications
634400		3m	254µm	10 kg	ANSI®/NEMA® GR1	CSA-US, UL, cUL, CSA
635800		3m	254µm	3.8 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	CSA, RUS, CSA-US, cUL, UL
635800ESB		3m	254µm	3.8 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	
635803		3m	330µm	3.9 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	RUS, UL, cUL
635830		0.9m	254µm	1.2 kg	IEC® EN 62561-2	
635840		1.2m	254µm	1.5 kg	IEC® EN 62561-2	
635843		1.2m	330µm	1.5 kg	IEC® EN 62561-2	
635850		1.5m	254µm	1.9 kg	IEC® EN 62561-2	
635860		1.8m	254µm	2.3 kg	IEC® EN 62561-2	
6358660		2m	254µm	2.48 kg	IEC® EN 62561-2	
635870		2.1m	254µm	2.9 kg	IEC® EN 62561-2	
635880	635880	2.4m	254µm	3 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	RUS, UL
635880ESB		2.4m	254µm	3 kg	IEC® EN 62561-2	
635883		2.4m	330µm	3 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	RUS, UL

ADDITIONAL PRODUCT DETAILS

For rods to be listed to UL® 467, they must be at least 8' (2.44 m) in length.

IEC® EN 62561-2 supercedes EN 50164-2.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including nickel, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.