

# Front Panel, Unshielded, Bottom Hinged

Unshielded front panel bottom hinged.

## FEATURES

Front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails



|                        |                            |
|------------------------|----------------------------|
| <b>Accessory Type:</b> | Front panel                |
| <b>Depth (D):</b>      | 2.5mm                      |
| <b>Finish:</b>         | Anodized                   |
| <b>Material:</b>       | Aluminum                   |
| <b>Product Type:</b>   | Front Panel                |
| <b>Type:</b>           | Front Panel without Handle |



## SPECIFICATIONS

| Table 1/2      |             |            |                  |                |              |             |
|----------------|-------------|------------|------------------|----------------|--------------|-------------|
| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish |
| 20838-280      | 3U          | 28HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-271      | 3U          | 42HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-272      | 3U          | 63HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-273      | 3U          | 84HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-277      | 4U          | 42HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-278      | 4U          | 63HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-279      | 4U          | 84HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-276      | 6U          | 84HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-275      | 6U          | 63HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |
| 20838-274      | 6U          | 42HP       | 1                | Hinged, Bottom | Anodized     | Conductive  |


Table 2/2

| Catalog Number | Treated Edges | Complies With                   | EMC Shielding | Height (H) | Width (W) |
|----------------|---------------|---------------------------------|---------------|------------|-----------|
| 20838-280      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4mm    | 141.9mm   |
| 20838-271      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4mm    | 213mm     |
| 20838-272      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4mm    | 319.7mm   |
| 20838-273      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4mm    | 426.4mm   |
| 20838-277      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 172.9mm    | 213mm     |
| 20838-278      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 172.9mm    | 319.7mm   |
| 20838-279      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 172.9mm    | 426.4mm   |
| 20838-276      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8mm    | 426.4mm   |
| 20838-275      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8mm    | 319.7mm   |
| 20838-274      | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8mm    | 213mm     |

## ADDITIONAL PRODUCT DETAILS

Front panel can be removed in opened position ( $> 135^\circ$ ).

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

