

# Cable/Conduit Clip



## FEATURES

Supports conduit to rod, wire or flange

Can also be used for flexible metallic tubing, armored cable, portable cables, control tubes and communications cable

Available for EMT, rigid, ENT, IMT, MC/AC and aluminum conduit

No installation tools required

**Material:** Spring Steel  
**Finish:** nVent CADDY Armour



## SPECIFICATIONS

| Catalog Number | Article Number | Outer Diameter (OD) | Static Load 1 (F1) | Static Load 2 (F2) | Static Load 3 (F3) | Certifications |
|----------------|----------------|---------------------|--------------------|--------------------|--------------------|----------------|
| K12            | 170670         | 24 mm Max           | 220N               | 445N               | 70N                | UL, cUL, ITB   |
| K16            | 170680         | 30 mm Max           | 220N               | 445N               | 70N                | ITB, UL, cUL   |
| K20            | 170690         | 42 mm Max           | 220N               | 445N               | 100N               | cUL, ITB, UL   |
| K8             | 170660         | 18 mm Max           | 220N               | 445N               | 70N                | cUL, UL        |
| KX             | 170870         | 12 mm Max           |                    |                    |                    | cUL, UL        |

## ADDITIONAL PRODUCT DETAILS



May require dedicated drop wire/rod and EC311. Consult local authority.


For horizontal application only when installing conduit.

| Part Number | Outer Diameter | Rod Size |
|-------------|----------------|----------|
| K12         | 14 mm - 20 mm  | M12      |
| K12         | 16 mm - 22 mm  | M8; M10  |
| K12         | 18 mm - 24 mm  | M4; M10  |
| K16         | 26 mm - 30 mm  | M4; M10  |
| K20         | 30 mm - 42 mm  | M4; M6   |
| K16         | 22 mm - 24 mm  | M12      |
| K16         | 24 mm - 26 mm  | M8; M6   |
| K20         | 20 mm - 36 mm  | M12      |
| K20         | 25 mm - 38 mm  | M8; M6   |

| Part Number | Outer Diameter | Flange Thickness |
|-------------|----------------|------------------|
| K12         | 16 mm - 22 mm  | 3 mm - 7 mm      |
| K12         | 14 mm - 20 mm  | 8 mm - 10 mm     |
| K12         | 12 mm - 19 mm  | 11 mm - 13 mm    |
| K16         | 24 mm - 28 mm  | 3 mm - 7 mm      |
| K16         | 20 mm - 26 mm  | 8 mm - 10 mm     |
| K16         | 19 mm - 24 mm  | 11 mm - 13 mm    |
| K20         | 28 mm - 40 mm  | 3 mm - 7 mm      |
| K20         | 26 mm - 38 mm  | 8 mm - 10 mm     |
| K20         | 21 mm - 35 mm  | 11 mm - 13 mm    |

## DIAGRAMS





## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.



[nVent.com/ENDDT](http://nVent.com/ENDDT) 3