


Conduit Trapeze CCT2



The nVent CADDY Conduit Trapeze CCT2 range is a fast and cost-effective method to install smaller feeder circuits of conduit in overhead trapeze installations. The CCT2 series eliminates reduces installation time and material cost by eliminating the need for traditional fasteners, making it an ideal solution for contractors looking to maximize installation efficiency.

FEATURES

Ideal for larger branch circuits

Accommodates ½ in threaded rod trapeze drops

Up to 25% material savings over traditional methods

Reduces installation time up to 50%

Complies with UL® 2239

Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Table 1/2

Catalog Number	Number of Conduits	Rod Size (RS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Hole Size 3 (HS3)	Hole Size 4 (HS4)
CCT2X12	4	10	14.29 mm	7.14 mm	7.14mm	60mm
CCT2X24	8	10	14.29 mm	7.14 mm	7.14mm	60mm
CCT2X36	12	10	14.29 mm	7.14 mm	7.14mm	60mm
CCT2X96	32	10	14.29 mm	7.14 mm	7.14mm	60mm

Table 2/2


Catalog Number	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Length 4 (L4)	Length (L)
CCT2X12	305 mm	356 mm	76.2mm	76.2 mm	356mm
CCT2X24	610 mm	660 mm	76.2mm	76.2 mm	660mm
CCT2X36	914 mm	965 mm	76.2mm	76.2 mm	965mm
CCT2X96	2438 mm	2489 mm	76.2mm	76.2 mm	2489mm

ADDITIONAL PRODUCT DETAILS

For 1/2" threaded rod trapeze drops, use washer or SN50.

The table contains maximum conduit size values.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

