

Conduit Trapeze CCT1, 48 Number of Conduits, 88.8"

CATALOG NUMBER

CCT1X90



The nVent CADDY Conduit Trapeze CCT1 range is a fast and cost-effective method to install smaller branch circuits of conduit in overhead trapeze installations. The CCT1 series reduces installation time and material cost by eliminating the need for traditional fasteners, making it an ideal solution for contractors looking to maximize installation efficiency.

FEATURES

Ideal for smaller branch runs

Shot fire flange for direct attachment to ceiling/deck

Accommodates 3/8" and 1/4" threaded rod trapeze drops

Up to 25% material savings over traditional methods

Reduces installation time up to 50%

Complies with UL® 2239



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Number of Conduits: 48

Rod Size (RS): 10

Hole Size 1 (HS1): 11.11 mm

Hole Size 2 (HS2): 7.14 mm

Hole Size 3 (HS3): 3.17mm

Hole Size 4 (HS4): 34.9mm

Length 1 (L1): 2210 mm

Length 2 (L2): 2256 mm

Length 3 (L3): 46.04mm


Length 4 (L4): 46.04 mm

ADDITIONAL PRODUCT DETAILS

For 3/8" and 1/4" threaded rod trapeze drops, use washer or SN25 for 1/4" threaded rod applications.

The table contains maximum conduit size values.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

