

nVent CADDY Flared Slip Coupler

The nVent CADDY Flared Slip Couplers are designed for quick and simple conduit rack installations. The integrated flare helps align each piece of conduit to easily join and install prefabricated conduit racks. This design allows the coupler to simply slide over the conduit and have visual confirmation of correct insertion depth through the center viewport. Contractors can enjoy a significantly decreased amount of ladder time for overhead installations.

FEATURES

Designed for EMT conduit

Fast and simple installation

Center viewport assists in conduit placement



SPECIFICATIONS

Catalog Number	Length (L)	Width (W)	Height (H)	Depth (D)	Certifications
SC0050	45.592mm	26.492 mm	38.074 mm	18.516mm	
SC0075	55.498mm	33.019 mm	44.602 mm	24.002mm	UL, cUL
SC0100	69.088mm	41.275 mm	52.705 mm	30.099mm	cUL, UL
SC0125	84.455mm	49.022 mm	60.706 mm	38.989mm	cUL, UL
SC0150	98.348mm	60.655 mm	72.339 mm	45.008mm	cUL, UL
SC0200	106.349mm	72.39 mm	84.074 mm	56.743mm	UL, cUL
SC0250	122.631mm	97.891 mm	111.378 mm	74.167mm	UL, cUL
SC0300	126.974mm	112.014 mm	125.501 mm	90.22mm	UL, cUL
SC0350	139.166mm	133.146 mm	146.634 mm	103.04mm	UL, cUL
SC0400	144.144mm	145.999 mm	159.486 mm	115.9mm	UL, cUL

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

