

nVent CADDY Speed Link SLC with Threaded Stud End



The nVent CADDY Speed Link SLC with Threaded Stud End delivers a fast, dependable way to suspend duct from structural supports, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC with Threaded Stud End helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

FEATURES

Includes wire and is assembled to a threaded stud end fitting

Quickly and easily attaches to structural supports

Attaches to structures with threaded anchors or devices with threaded holes

Connects directly to threaded devices in trapeze assemblies, light fixtures, HVAC assemblies or signage

Compatible with nVent CADDY Speed Link SLS Locking Device and nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

Material:	Steel
Finish:	Electrogalvanized
Static Load Safety Factor:	5:1
Complies With:	SMACNA HVAC-DCS

SPECIFICATIONS

Catalog Number	Wire Rope Diameter	Wire Rope Length	Rod Size (RS)	Screw Length (L)	Static Load
SLC2L10SE375	2 mm	10m	0.375	44.5mm	440N
SLC2L3SE375	2 mm	3m	0.375	44.5mm	440N
SLC2L5SE375	2 mm	5m	0.375	44.5mm	440N

Catalog Number	Wire Rope Diameter	Wire Rope Length	Rod Size (RS)	Screw Length (L)	Static Load
SLC3L10SE375	3 mm	10m	0.375	44.5mm	890N
SLC3L3SE375	3 mm	3m	0.375	44.5mm	890N
SLC3L5SE375	3 mm	5m	0.375	44.5mm	890N
SLC15L10SE375	1.5 mm	10m	0.375	44.5mm	195N
SLC15L3SE375	1.5 mm	3m	0.375	44.5mm	195N
SLC15L5SE375	1.5 mm	5m	0.375	44.5mm	195N

Height (H): 55 mm
Width (W): 19 mm
Thickness (T): 12.5 mm

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical
 Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

