

nVent CADDY Speed Link SLK with Loop



FEATURES

Complete system includes wire, locking device and pre-assembled loop end fitting

Easy and flexible solution attaches to building structures

Wire rope wraps around structure and through loop for quick installation

Ideal for attaching to purlins, beams and other structural members

Works well in tight or confined spaces

Loop attaches directly to pipe, ductwork or other hanging assemblies

Material: Steel; Polypropylene; Zinc Alloy
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS



SPECIFICATIONS


Table 1/2

Catalog Number	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)	Width (W)	Thickness (T)
SLK15L1LP	1.5 mm	1m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L1LPR2	1.5 mm	1m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L2LP	1.5 mm	2m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L2LPR2	1.5 mm	2m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L3LP	1.5 mm	3m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L3LPR2	1.5 mm	3m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L5LP	1.5 mm	5m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L5LPR2	1.5 mm	5m	101.6mm	55 mm	19 mm	12.5 mm
SLK15L7LP	1.5 mm	7m	101.6mm	55 mm	19 mm	12.5 mm
SLK2L10LP	2 mm	10m	101.6mm	55 mm	19 mm	12.5 mm
SLK2L1LP	2 mm	1m	101.6mm	55 mm	19 mm	12.5 mm

Catalog Number	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)	Width (W)	Thickness (T)
SLK2L2LP	2 mm	2m	101.6mm	55 mm	19 mm	12.5 mm
SLK2L3LP	2 mm	3m	101.6mm	55 mm	19 mm	12.5 mm
SLK2L5LP	2 mm	5m	101.6mm	55 mm	19 mm	12.5 mm
SLK3L10LP	3 mm	10m	101.6mm	62 mm	24 mm	16 mm
SLK3L3LP	3 mm	3m	101.6mm	62 mm	24 mm	16 mm
SLK3L5LP	3 mm	5m	101.6mm	62 mm	24 mm	16 mm

Table 2/2

Catalog Number	Angle (a)	Static Load	Certifications
SLK15L1LP	90 ° Max	195N	cUL, SMACNA, UL
SLK15L1LPR2	90 ° Max	195N	UL, SMACNA, cUL
SLK15L2LP	90 ° Max	195N	SMACNA, cUL, UL
SLK15L2LPR2	90 ° Max	195N	cUL, UL, SMACNA
SLK15L3LP	90 ° Max	195N	UL, cUL, SMACNA
SLK15L3LPR2	90 ° Max	195N	cUL, UL, SMACNA
SLK15L5LP	90 ° Max	195N	cUL, SMACNA, UL
SLK15L5LPR2	90 ° Max	195N	UL, SMACNA, cUL
SLK15L7LP	90 ° Max	195N	UL, cUL, SMACNA
SLK2L10LP	90 ° Max	440N	SMACNA, UL, cUL
SLK2L1LP	90 ° Max	440N	SMACNA, UL, cUL
SLK2L2LP	90 ° Max	440N	UL, SMACNA, cUL
SLK2L3LP	90 ° Max	440N	SMACNA, cUL, UL
SLK2L5LP	90 ° Max	440N	UL, SMACNA, cUL
SLK3L10LP	90 ° Max	890N	SMACNA
SLK3L3LP	90 ° Max	890N	SMACNA
SLK3L5LP	90 ° Max	890N	SMACNA



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

