

Telescoping Pipe Stand



The nVent CADDY Telescoping Pipe Stand is an adjustable and flexible solution for supporting horizontal pipe runs using a traditional V-Saddle or bolt flange attachment method. The design ensures a faster installation that quickly adapts to a variety of pipe sizes and heights from the floor. The unique V-bolt fastener—with built in nVent CADDY Rod Lock Technology and flange attachment tabs—can adapt to a large range of bolt patterns, sizes and pipe diameters, ultimately reducing inventory and the amount of components needed with over two-thirds savings. Offering a complete out-of-the-box assembly, the nVent CADDY Telescoping Pipe Stand is a contemporary solution for pipe runs.

FEATURES

Supports and fastens low-to-the-ground horizontal pipe runs

Telescoping post provides fast vertical height adjustment

Designed to minimize fabrication and reduce installation time of a complete stand compared to traditional methods

Integrated weep hole at bottom of stand provides drainage for condensation

Includes four holes for anchoring base to floor

Conforms with Federal Specification WW-H-171 (Type 36, 37, 38, 39), Manufacturers Standardization Society ANSI/MSS SP-58 (Type 36, 37, 38)

Finish: Electrogalvanized

Material: Steel



SPECIFICATIONS

Table 1/2

Catalog Number	NB/DN	A	B	C	D	E
CTS10	125 - 250	605 - 1070 mm	365 mm	216 mm	165 mm	135 - 260 mm
CTS04	25 - 100	341 - 554 mm	173 mm	165 mm	127 mm	78 - 154 mm
CTSS04	25 - 100	353 - 554 mm	173 mm	165 mm	127 mm	78 - 154 mm
CTSS10	125 - 250	410 - 655 mm	365 mm	216 mm	165 mm	135 - 260 mm

Catalog Number	NB/DN	A	B	C	D	E
CTS10A24	300 - 600		686 mm			

Table 2/2					
Catalog Number	G	Hole Size (HS)	Static Load	Unit Weight	Certifications
CTS10	608 - 1021 mm	16 mm	13540N	16.1 kg	
CTS04	602 - 965 mm	16 mm	10660N	11.8 kg	OSHDPD/HCAI
CTSS04	405 - 595 mm	16 mm	10660N	8.4 kg	
CTSS10	405 - 595 mm	16 mm	13540N	14.3 kg	
CTS10A24		16 mm		3.4 kg	


ADDITIONAL PRODUCT DETAILS

When insulating pipe install V-bolt after insulation.

Telescoping pipe stand can accommodate pipes up to 24" when v-bolt is removed. Installer must determine weight of the pipe and proper spacing when supporting larger sizes.

2:1 safety factor used for metric Static Load. 3.5:1 safety factor used for imperial Static Load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

