

Hol-Sealers Hole Seal

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals . Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.



INDUSTRY STANDARDS

UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)

Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66

FEATURES

Available in multiple colors and sizes

Oil-resistant gasket provided

Steel model has plated stud (10-32x5/8) and wing nut

Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
AS056MSS	15506	Stainless Steel 304	Polished			1.5mm
AS056M	15505	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS056MFB	16485	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
AS056MLG	16076	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm
AS056CB	15645	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
ASPBGSS	59420	Stainless Steel 304	Polished			1.5mm
ASPBG	59690	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS100LG	15576	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm
AS100SS 	59460	Stainless Steel 304	Polished			1.5mm
AS100 	59730	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS050 	59700	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS050LG	15574	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm
AS050SS 	59430	Stainless Steel 304	Polished			1.5mm
AS350SS	15961	Stainless Steel 304	Polished			1.5mm
AS250SS	15957	Stainless Steel 304	Polished			1.5mm
AS125LG	15578	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm
AS150SS 	59480	Stainless Steel 304	Polished			1.5mm
AS400SS	15962	Stainless Steel 304	Polished			1.5mm
AS125SS 	59470	Stainless Steel 304	Polished			1.5mm
AS075 	59710	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm

Table 2/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
AS150LG	15581	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm
ASPB 	59720	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS300SS	15958	Stainless Steel 304	Polished			1.5mm
AS300 	59780	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS150 	59750	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS125 	59740	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS400 	59800	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS200 	59760	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
ASPBSS 	59450	Stainless Steel 304	Polished			1.5mm
AS200SS 	59490	Stainless Steel 304	Polished			1.5mm
AS250 	59770	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS075SS 	59440	Stainless Steel 304	Polished			1.5mm
ASBBLG	15582	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm
AS350	59790	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm
AS200LG	15577	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm
AS075LG	15575	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE