

Conduit Trapeze CCT2, 12 Number of Conduits, 38"

CATALOG NUMBER

CCT2X36

The nVent CADDY Conduit Trapeze CCT2 range is a fast and cost-effective method to install smaller feeder circuits of conduit in overhead trapeze installations. The CCT2 series eliminates reduces installation time and material cost by eliminating the need for traditional fasteners, making it an ideal solution for contractors looking to maximize installation efficiency.

FEATURES

Ideal for larger branch circuits

Accommodates ½ in threaded rod trapeze drops

Up to 25% material savings over traditional methods

Reduces installation time up to 50%

Complies with UL® 2239



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Number of Conduits: 12

Rod Size (RS): 10

Hole Size 1 (HS1): 14.29 mm

Hole Size 2 (HS2): 7.14 mm

Hole Size 3 (HS3): 7.14mm

Hole Size 4 (HS4): 60mm

Length 1 (L1): 914 mm

Length 2 (L2): 965 mm

Length 3 (L3): 76.2mm

Length 4 (L4): 76.2 mm


Length (L): 965mm

ADDITIONAL PRODUCT DETAILS

For 1/2" threaded rod trapeze drops, use washer or SN50.

The table contains maximum conduit size values.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

