

Speed Link SLS Locking Device with Duct Bracket, 2 mm Wire

CATALOG NUMBER

SLS2DBK

The nVent CADDY Speed Link SLS Duct Bracket delivers a fast, dependable way to suspend square duct, enabling crews to move quickly and reduce time on elevated surfaces. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.



FEATURES

Ideal for modular assemblies

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

Ready-to-use out-of-the-box, eliminating the need for cutting or preparing sections of strut

Prevents wire rope from damaging ductwork

Designed to work with wire in order to fit application needs (sold separately)

Compatible with the nVent CADDY Speed Link SLS Locking Device and nVent CADDY Speed Link SLC System

PRODUCT ATTRIBUTES

Wire Diameter: 2mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDDT](https://www.nvent.com/ENDDT)

