

nVent CADDY Speed Link SLC with Nail Gun Bracket

The nVent CADDY Speed Link SLC with Nail Gun Bracket delivers a fast, dependable way to suspend duct from concrete, steel or composite metal decking, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC with Nail Gun Bracket helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

FEATURES

Includes wire and is assembled to a nail gun bracket end fitting

Quickly and easily attaches to concrete, steel or composite metal decking

Clips onto the nozzle of gas or battery-actuated nail guns, allowing for hands-off installation at structure or from the floor using a pole

Longer leg angle bracket for tool clearance

Compatible with nVent CADDY Speed Link SLS Locking Device and nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

Material:	Steel
Finish:	Electrogalvanized
Static Load Safety Factor:	5:1
Complies With:	SMACNA HVAC-DCS


SPECIFICATIONS

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	Static Load
SLC2L10GBSF	2 mm	10m	38.1 mm	25.4 mm	440N
SLC2L3GBSF	2 mm	3m	38.1 mm	25.4 mm	440N
SLC2L5GBSF	2 mm	5m	38.1 mm	25.4 mm	440N

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	Static Load
SLC15L10GBSF	1.5 mm	10m	38.1 mm	25.4 mm	195N
SLC15L3GBSF	1.5 mm	3m	38.1 mm	25.4 mm	195N
SLC15L5GBSF	1.5 mm	5m	38.1 mm	25.4 mm	195N

Angle (a): 90 ° Max

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

