

# Drop-In Anchor, Steel, EG, M12 Hole, 50 mm

## CATALOG NUMBER

**CAM12050**



## FEATURES

Internal thread provides easy removal and serviceability

Installs flush or below the base surface

Suitable for redundant non-structural systems on cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire



## PRODUCT ATTRIBUTES

Article Number: 400415

Material: Steel

Finish: Electrogalvanized

Hole Size (HS): 12 mm

Length (L): 50mm

Drill Bit Diameter: 15mm

Characteristic Axial Loads from ETA 14-0068 - for redundant non-structural systems

| Part Number | Cracked Concrete C20/25 | Non-Cracked Concrete C20/25 | Standard Embedment Depth |
|-------------|-------------------------|-----------------------------|--------------------------|
| CAM6030     | 0.80 kN                 | 0.80 kN                     | 25 mm                    |
| CAM8030     | 1.20 kN                 | 1.20 kN                     | 30 mm                    |
| CAM10040    | 1.70 kN                 | 1.70 kN                     | 40 mm                    |
| CAM12050    | 2.60 kN                 | 2.60 kN                     | 50 mm                    |
| CAM8030S6   | 1.20 kN                 | 1.20 kN                     | 25 mm                    |
| CAM10040S6  | 1.70 kN                 | 1.70 kN                     | 40 mm                    |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

