

Threaded Coupler for Copper-Bonded Ground Rod, Threaded

FEATURES

High-strength couplings are threaded and chamfered at both ends for easy driving

Corrosion-resistant couplings ensure permanent, low resistance copper-to-copper connections



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	Material	Ground Rod Diameter, Nominal	Length (L)	Thread Size (TS)	Unit Weight
CR100		Silicon Bronze	1"	99.1mm	1" UNC	0.35 kg
CR12S		Bronze	9/16"	63.5mm	9/16" UNC	0.07 kg
CR58	158040	Bronze	5/8"	61mm	5/8" UNC	0.09 kg
CR34		Bronze	3/4"	76.2mm	3/4" UNC	0.15 kg

Table 2/2

Catalog Number	Article Number	Complies With	Certifications
CR100		EN IEC 62561-2	cUL, UL
CR12S		EN IEC 62561-2	UL, cUL, CSA, CSA-US
CR58	158040	EN IEC 62561-2	UL, cUL, CSA-US, RUS, CSA

Catalog Number	Article Number	Complies With	Certifications
CR34			RUS, CSA-US, UL, cUL, CSA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical
 Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

