

Easy Swap LFT Cold Plate, Short

New

CATALOG NUMBER

20740-004



The Easy Swap LFT Cold Plate, short Version, gets installed into the adjacent slot of the board that should be liquid cooled. The short version is designed for 4 HP boards with heat sinks across the whole board. A dedicated board heat sink is required to make the contact to the Cold Plate the cold plate. Generic step file can be found in the resource section. The thermal gap pad that is within the scope of delivery can be assembled either on the heat sink or the cold plate. The Cold Plate comes with 2x 700 mm hoses to be connected to the cooling circuitry or other liquid sources.

FEATURES

- Liquid Flow Through Cold Plate for 3U Standard Eurocard Boards
- To be assembled in adjacent slot of board to be cooled, behind mezzanine board of 8 HP front panel
- Up to 200 W of cooling capacity at 50°C environmental temperature
- Accepts demineralized water or Water Glycol mix (25% Glycol recommended)
- Mating heat sink on board mandatory
- To be attached to Cooling Circuitry either with Quick Disconnects or the Direct Connection Set



PRODUCT ATTRIBUTES

- Depth: 160mm
- Material: Copper; Stainless Steel
- Package Quantity: 1
- Product Family: Liquid Board Cooling
- Product Type: Conductor Block
- Type: Liquid Cold Plate
- Width: 20.32mm
- Works With: Subracks

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADDITIONAL PRODUCT DETAILS

Please order the Connection Set and Cooling Circuitry separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

