


# On Board Rack



Suitable for ongoing vibrations, shock, high temperatures, and high humidity.

## FEATURES

For mobile railway applications

Suitable for ongoing vibrations, shock, high temperatures, and high humidity

Suitable for 1, 2, or 3 U SNCF subracks (NF F61-005, CF 60-002)

Rear side is equipped for standard connectors; crossbar can be custom-coded for the SNCF coding pins

Crossbar with integrated cable channel

Several racks can be stacked or fitted in rows

Produced using a welding process, certified to EN 15085 (CL2)

Stainless Steel welds passivated to prevent corrosion

|                        |                                |
|------------------------|--------------------------------|
| <b>Depth:</b>          | 341.8mm                        |
| <b>Finish:</b>         | Raw                            |
| <b>Complies With:</b>  | SNCF NFF 61005; SNCF NFF 60002 |
| <b>Frame Material:</b> | Stainless Steel                |
| <b>Static Load:</b>    | 25kg                           |
| <b>Product Type:</b>   | Rack                           |



## SPECIFICATIONS

| Catalog Number | Rack Height | Height  | Width    | Package Quantity | Material        | Rack Width |
|----------------|-------------|---------|----------|------------------|-----------------|------------|
| 10170-012      | 6U          | 290mm   | 496.4mm  | 1                | Stainless Steel | 84HP       |
| 10170-013      | 6U          | 290mm   | 252.65mm | 1                | Stainless Steel | 36HP       |
| 10170-014      | 3U          | 156.7mm | 496.4mm  | 1                | Stainless Steel | 84HP       |
| 10170-015      | 3U          | 156.7mm | 252.65mm | 1                | Stainless Steel | 36HP       |
| 10170-016      | 9U          | 423.4mm | 496.4mm  | 1                | Stainless Steel | 84HP       |
| 10170-017      | 9U          | 423.4mm | 252.65mm | 1                | Stainless Steel | 36HP       |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.