

nVent CADDY Cat HP J-Hook, PG, Painted, Orange, 100 mm dia

CATALOG NUMBER

CAT64HPOR



nVent CADDY Cat HP J-Hooks are the foundation of the nVent CADDY Cat HP System. The revamped nVent CADDY Cat HP J-Hook offers contractors three unique, UL-certified attachment methods out of the box—wall, ceiling, and threaded rod installations. This added functionality enables contractors to reduce SKU inventory while maintaining efficiency and continued progress on the jobsite with the most common structural attachment methods.

The modernized design of the nVent CADDY Cat HP J-Hook is engineered to provide optimal support and protection for today's rapidly evolving, high-performing low voltage cable. Contractors can feel confident utilizing the nVent CADDY Cat HP J-Hook due to its installation versatility, superior cable support and protection, and technical certifications.

FEATURES

One through-hole for easier installation of threaded rod

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



PRODUCT ATTRIBUTES

Article Number: 181137

Material: Steel

Finish: Pregalvanized, Painted;Painted

Color: Orange

Diameter (Ø): 100 mm

Area: 9987mm²

Cable Capacity, Cat 5e: 330

Cable Capacity, Cat 6: 220

Cable Capacity, Cat 6A: 140

Height (H): 188.47 mm

Static Load: 267N

ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

Fire Rated Power Cable Capacity (Distance between J-hooks must not exceed 500 mm center to center)									
Part Number		CAT16HP		CAT32HP CAT48HP		CAT64HP		CAT64HP	
Configuration		Single Layer		Single Layer		Single Layer		Double Layer	
Max Load per Support [kg/m]		0.8 kg/m		1.4 kg/m		2.6 kg/m		2 kg/m	
Cable	Linear Weight of the Cable [kg/m]	Number of Cables	Classification	Number of Cables	Classification	Number of Cables		Classification	
4x1,5 (N)HXH FE180 E30-E60	0.234	3	E30	5	E30 E60	11	E30 E60	8	E30 E60
5x1,5 (N)HXH FE 180 E30-E60	0.277	2		5	E30	9	E30	7	E30
7x1,5 (N)HXH FE 180 E30-E60	0.330	2		4		7		6	
12x1,5 (N)HXH FE 180 E30-E60	0.513	1		2		5		3	
19x1,5 (N)HXH FE 180 E30-E60	0.715	1		1		3		2	
24x1,5 (N)HXH FE 180 E30-E60	0.901	-		1		2		2	
30x1,5 (N)HXH FE 180 E30-E60	1.052	-		1		2		1	
2x2,5 (N)HXH FE 180 E30-E60	0.178	4	E30	-	-	-	-	-	-
3x2,5 (N)HXH FE 180 E30-E60	0.250	3		-	-	-	-	-	-
4x2,5 (N)HXH FE 180 E30-E60	0.296	2		-	-	-	-	-	-
5x2,5 (N)HXH FE 180 E30-E60	0.352	2		-	-	-	-	-	-
4x1,5 (N)HXH FE 180 E90	0.234	3	E30 E60 E90	5	E30 E60 E90	11	E30 E60 E90	8	E30 E60 E90
5x1,5 (N)HXH FE 180 E90	0.277	2		5		9		7	
7x1,5 (N)HXH FE 180 E90	0.330	2		4		7		6	

12x1,5 (N)HXH FE 180 E90	0.511	1	2	5	3	
24x1,5 (N)HXH FE 180 E90	0.901	-		1	2	2
2x2x0,8 JE- H(St)H...Bd FE180 E30- E90	0.060	13	E30	-	-	-
4x2x0,8 JE- H(St)H...Bd FE180 E30- E90	0.102	7		-	-	-
8x2x0,8 JE- H(St)H...Bd FE180 E30- E90	0.221	3		-	-	-
12x2x0,8 J E- H(St)H...Bd FE180 E30- E90	0.281	2		-	-	-
16x2x0,8 J E- H(St)H...Bd FE180 E30- E90	0.326	2		-	-	-
20x2x0,8 J E- H(St)H...Bd FE180 E30- E90	0.421	1		-	-	-
32x2x0,8 J E- H(St)H...Bd FE180 E30- E90	0.588	1		-	-	-
40x2x0,8 J E- H(St)H...Bd FE180 E30- E90	0.761	1		-	-	-
Fire rating applicable when linking specified J-hook to the following components		Fire rating applicable to the following riveted assemblies				
Part number		Part number				
CATHPAN		CAT16HPAB		CAT32HPAB	CAT48HPAB	CAT64HPAB
CATHPA4		CAT16HPBCB		CAT32HPAF AB3	CAT48HPAF AB3	CAT64HPAFAB3
CATHPA6		CAT16HPBC200B		CAT32HPAF AB4	CAT48HPAF AB4	CAT64HPAFAB4
CATHPTM		CAT16HP24SM		CAT32HPAF AB6	CAT48HPBC B	CAT64HPBCB

CATHPBCB	CAT16HP58SM	CAT32HPBCB	CAT48HP58SM	CAT64HPBC200B
CATHPBC200B	CAT16HP912SM	CAT32HPBC200B	CAT48HP912SM	CAT64HP58SM
CATHP912SM	CAT16HP24	CAT32HP24SM	CAT48HP24	CAT64HP912SM
CATHP24	CAT16HP58	CAT32HP912SM	CAT48HP58	CAT64HP24
CATHP58	-	CAT32HP24	-	-
CATHP912	-	-	-	-

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

