


Speedway Cable Ladder Inside Riser, 90°



FEATURES


- Creates a 90° inside riser elevation change for cable tray
- Provides optimal support for high-performance low voltage and data cables
- Innovative SPEEDLOK integrated coupling system
- Safety edge protects cables during installation
- Slotted side channel, eliminating field drilling for cut-to-length applications
- IEC 61537 load rating and earthing compliant
- Responsive design and layout services, including seismic

Material: Steel
Finish: Hot-Dip Galvanized



SPECIFICATIONS

Catalog Number	Article Number	Width (W)	Angle (a)	A	B	C	D
CL110X150IR90HD	840500	150 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X300IR90HD	840510	300 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X450IR90HD	840520	450 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X600IR90HD	840530	600 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X750IR90HD	840540	750 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X900IR90HD	840550	900 mm	90 °	410 mm	410 mm	580 mm	80 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

