

# Quick Grip Jr. Lateral Sway Brace, 1 1/4" Pipe, 32 DN

## CATALOG NUMBER

**CSBQIKCL0125EG**



## FEATURES

Easy two-step installation eliminates extra trips between structure and service pipe

Works with 1" and 1 1/4" (25 mm and 32 mm) brace pipes to reduce inventory

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing



## PRODUCT ATTRIBUTES

Article Number: 404374

Material: Steel

Finish: Electrogalvanized

Pipe Size: 1 1/4"

NB/DN: 32

Height (H): 136.5 mm

Width (W): 74.4 mm

Brace Pipe Size: 1" - 1 1/4"

Brace NB/DN: 25 - 32 mm

| FM Loads       |                       |                                                          |           |           |           |
|----------------|-----------------------|----------------------------------------------------------|-----------|-----------|-----------|
| Part Number    | Service Pipe Schedule | Lateral                                                  |           |           |           |
|                |                       | Horizontal Capacity per Installation Angle from Vertical |           |           |           |
|                |                       | 30° - 44°                                                | 45° - 59° | 60° - 74° | 75° - 90° |
| CSBQIKCL0100EG | EN10255 L (Lightwall) | 1290 N                                                   | 1830 N    | 2200 N    | 2445 N    |
|                | EN10255 M (10)        | 665 N                                                    | 935 N     | 1245 N    | 1400 N    |
|                | EN10255 H (40)        | 2115 N                                                   | 2960 N    | 3670 N    | 4115 N    |
| CSBQIKCL0125EG | EN10255 L (Lightwall) | 1290 N                                                   | 1830 N    | 2200 N    | 2445 N    |
|                | EN10255 M (10)        | 665 N                                                    | 935 N     | 1245 N    | 1400 N    |
|                | EN10255 H (40)        | 2115 N                                                   | 2960 N    | 3670 N    | 4115 N    |
| CSBQIKCL0150EG | EN10255 L (Lightwall) | 1290 N                                                   | 1830 N    | 2200 N    | 2445 N    |
|                | EN10255 M (10)        | 665 N                                                    | 935 N     | 1245 N    | 1400 N    |
|                | EN10255 H (40)        | 2115 N                                                   | 2960 N    | 3670 N    | 4115 N    |
| CSBQIKCL0200EG | EN10255 L (Lightwall) | 1735 N                                                   | 2445 N    | 2980 N    | 3335 N    |
|                | EN10255 M (10)        | 1555 N                                                   | 2225 N    | 2760 N    | 3070 N    |
|                | EN10255 H (40)        | 2180 N                                                   | 3070 N    | 3780 N    | 4225 N    |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

