

Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.
Prepared for high cable densities and 19" integration.

FEATURES

- Preconfigured, ready to use cabinet
- Static load-carrying capacity up to 1600 kg
- Ingress protection class IP 20
- Installation of different Networking equipment possible
- Integrated vertical and horizontal cable management
- Can be easily integrated into aisle containment system

Frame Material: Steel
Material: Steel
Product Type: Rack

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Cladding Material	Frame Color	Height	Frame Color Code	Cladding Color
10630-027	42U	Steel	Black Grey	2000mm	RAL 7021	Black Grey
10630-028	42U	Steel	Black Grey	2000mm	RAL 7021	Black Grey

Table 2/2

Catalog Number	Width	Depth	Static Load	Cladding Color Code	Package Quantity	Dynamic Load	Finish
10630-027	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	Powder Coated
10630-028	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.