

115 Standard Duty Loop Hanger



The 115 Standard Duty Loop Hanger is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2" to 4" sizes) help protect pipes from coming into contact with any sharp edges of the hanger.

FEATURES

Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)

Retained insert nut helps ensure the loop hanger and insert nut stay together

Recommended for the suspension of stationary non-insulated pipe lines

Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping


Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	A	B	C	Static Load
1150250EG	182798	65	76 mm	150.8 mm	87.3 mm	50.8 mm	2340N
1150300EG	182804	80	89 mm	166.3 mm	88.2 mm	49.7 mm	2340N
1150400EG	182805	100	114 mm	192.5 mm	100.9 mm	48.9 mm	2890N
1150500EG	182799	125	140 mm	232.7 mm	120 mm	57.1 mm	4450N
1150600EG	182806	150	165 mm	286.6 mm	160.4 mm	84.1 mm	4450N
1150800EG		200	219 mm	327.1 mm	175.1 mm	73.4 mm	4450N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

